

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642415

Luminaire Tested: ML5615LSFL409FS1E - 592W - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 592W - 900LM - 5000K
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1293.1 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642415
CATALOG NUMBER: ML5615LSFL409FS1E - 592W - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642415

CATALOG NUMBER: ML5615LSFL409FS1E - 592W - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 100 | 98 | 97 | 96 | 95 | 94 | | | | | | | | | | | | | | | | | | | |
| 2 | 108 | 103 | 99 | 96 | 106 | 102 | 98 | 95 | 98 | 95 | 93 | 95 | 93 | 91 | 93 | 91 | 89 | 87 | | | | | | | | | | | | | | | | | | | |
| 3 | 103 | 97 | 92 | 88 | 101 | 95 | 91 | 87 | 93 | 89 | 86 | 90 | 87 | 84 | 88 | 85 | 83 | 81 | | | | | | | | | | | | | | | | | | | |
| 4 | 98 | 90 | 85 | 81 | 96 | 89 | 84 | 80 | 87 | 83 | 79 | 85 | 82 | 79 | 83 | 80 | 78 | 76 | | | | | | | | | | | | | | | | | | | |
| 5 | 93 | 85 | 79 | 75 | 92 | 84 | 79 | 75 | 82 | 78 | 74 | 81 | 77 | 73 | 79 | 76 | 73 | 71 | | | | | | | | | | | | | | | | | | | |
| 6 | 89 | 80 | 74 | 70 | 87 | 79 | 74 | 70 | 78 | 73 | 69 | 76 | 72 | 69 | 75 | 71 | 68 | 67 | | | | | | | | | | | | | | | | | | | |
| 7 | 85 | 76 | 70 | 66 | 83 | 75 | 69 | 66 | 74 | 69 | 65 | 73 | 68 | 65 | 71 | 68 | 65 | 63 | | | | | | | | | | | | | | | | | | | |
| 8 | 81 | 72 | 66 | 62 | 80 | 71 | 66 | 62 | 70 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 61 | 60 | | | | | | | | | | | | | | | | | | | |
| 9 | 77 | 68 | 62 | 58 | 76 | 67 | 62 | 58 | 67 | 62 | 58 | 66 | 61 | 58 | 65 | 61 | 58 | 56 | | | | | | | | | | | | | | | | | | | |
| 10 | 74 | 65 | 59 | 55 | 73 | 64 | 59 | 55 | 63 | 58 | 55 | 63 | 58 | 55 | 62 | 58 | 55 | 54 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 168641 |
| 5° | 163335 |
| 10° | 141881 |
| 15° | 116860 |
| 20° | 90778 |
| 25° | 68863 |
| 30° | 49770 |
| 35° | 34095 |
| 40° | 21455 |
| 45° | 12571 |
| 50° | 5035 |
| 55° | 3289 |
| 60° | 2337 |
| 65° | 1494 |
| 70° | 1316 |
| 75° | 1403 |
| 80° | 1546 |
| 85° | 996 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12571 cd/sqm



TEST NUMBER: P642415

CATALOG NUMBER: ML5615LSFL409FS1E - 592W - 900LM - 5000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 187.2 | 14.5 |
| 10°-20° | 394.5 | 30.5 |
| 20°-30° | 362.4 | 28.0 |
| 30°-40° | 223.8 | 17.3 |
| 40°-50° | 87.5 | 6.8 |
| 50°-60° | 22.6 | 1.7 |
| 60°-70° | 9.0 | 0.7 |
| 70°-80° | 4.5 | 0.4 |
| 80°-90° | 1.7 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 944.1 | 73.0 |
| 0°-40° | 1167.8 | 90.3 |
| 0°-60° | 1277.9 | 98.8 |
| 0°-90° | 1293.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1293.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2136 | |
| 5° | 2061 | 187 |
| 15° | 1430 | 394 |
| 25° | 791 | 362 |
| 35° | 354 | 224 |
| 45° | 113 | 87 |
| 55° | 24 | 23 |
| 65° | 8 | 9 |
| 75° | 5 | 5 |
| 85° | 1 | 2 |
| 90° | 0 | |



TEST NUMBER: P642415

CATALOG NUMBER: ML5615LSFL409FS1E - 592W - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2136.3 |
| 2.5° | 2121.5 |
| 5° | 2061.2 |
| 7.5° | 1938.3 |
| 10° | 1770.0 |
| 12.5° | 1599.4 |
| 15° | 1429.9 |
| 17.5° | 1252.4 |
| 20° | 1080.6 |
| 22.5° | 928.2 |
| 25° | 790.6 |
| 27.5° | 662.0 |
| 30° | 546.0 |
| 32.5° | 442.5 |
| 35° | 353.8 |
| 37.5° | 277.6 |
| 40° | 208.2 |
| 42.5° | 159.3 |
| 45° | 112.6 |
| 47.5° | 64.8 |
| 50° | 41.0 |
| 52.5° | 31.9 |
| 55° | 23.9 |
| 57.5° | 18.2 |
| 60° | 14.8 |
| 62.5° | 12.5 |
| 65° | 8.0 |
| 67.5° | 5.7 |
| 70° | 5.7 |
| 72.5° | 4.6 |
| 75° | 4.6 |
| 77.5° | 3.4 |
| 80° | 3.4 |
| 82.5° | 2.3 |
| 85° | 1.1 |
| 87.5° | 1.1 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)