

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641857

Luminaire Tested: ML5612LSVWFL97FS1E - 693TBZB - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641857
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-112)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSVWFL97FS1E - 693TBZB - 900LM - 3000K
Description: ML56 RR, MILKY OPTIC, 6" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 913.2 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.21
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641857

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P641857

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82																			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	69	76	72	69	67																			
5	86	76	69	64	85	75	69	64	73	68	63	72	67	63	70	66	62	60																			
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	56	55																			
7	76	65	58	53	74	64	57	52	63	57	52	61	56	52	60	55	52	50																			
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	56	51	47	46																			
9	67	56	49	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42																			
10	63	52	45	40	62	51	45	40	50	44	40	49	44	40	49	44	40	38																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31330
5°	31268
10°	30939
15°	30522
20°	30003
25°	29409
30°	28574
35°	27124
40°	23866
45°	17064
50°	9961
55°	5257
60°	2467
65°	1025
70°	353
75°	233
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17064 cd/sqm



TEST NUMBER: P641857

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.8	5.9
10°-20°	151.7	16.6
20°-30°	223.5	24.5
30°-40°	250.3	27.4
40°-50°	169.7	18.6
50°-60°	53.9	5.9
60°-70°	9.1	1.0
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.0	47.0
0°-40°	679.3	74.4
0°-60°	902.9	98.9
0°-90°	913.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	913.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	572	
5°	568	54
15°	538	152
25°	486	224
35°	405	250
45°	220	170
55°	55	54
65°	8	9
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P641857

CATALOG NUMBER: ML5612LSVWFL97FS1E - 693TBZB - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	571.5
2.5°	570.4
5°	568.2
7.5°	562.5
10°	555.8
12.5°	547.9
15°	537.8
17.5°	527.7
20°	514.3
22.5°	500.8
25°	486.2
27.5°	469.3
30°	451.4
32.5°	431.2
35°	405.3
37.5°	373.9
40°	333.5
42.5°	279.6
45°	220.1
47.5°	163.9
50°	116.8
52.5°	82.0
55°	55.0
57.5°	37.1
60°	22.5
62.5°	13.5
65°	7.9
67.5°	3.4
70°	2.2
72.5°	1.1
75°	1.1
77.5°	1.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)