

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642465

Luminaire Tested: ML5615LSFL409FS1E - 593WB - 1200LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642465  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSFL409FS1E - 593WB - 1200LM - 5000K  
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1634.0 lumens  
Efficiency: N/A  
Efficacy: 121.9 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642465

CATALOG NUMBER: ML5615LSFL409FS1E - 593WB - 1200LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642465

CATALOG NUMBER: ML5615LSFL409FS1E - 593WB - 1200LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 99  | 98  | 97  | 96  | 95  | 94  |    |    |   |
| 2   | 108 | 103 | 99  | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 93  | 95  | 93  | 91  | 93  | 91  | 89  | 87  |    |    |   |
| 3   | 103 | 96  | 92  | 88  | 101 | 95  | 91  | 87  | 92  | 89  | 86  | 90  | 87  | 84  | 88  | 85  | 83  | 81  |    |    |   |
| 4   | 98  | 90  | 85  | 81  | 96  | 89  | 84  | 80  | 87  | 83  | 79  | 85  | 82  | 79  | 83  | 80  | 78  | 76  |    |    |   |
| 5   | 93  | 85  | 79  | 75  | 92  | 84  | 79  | 75  | 82  | 78  | 74  | 81  | 77  | 73  | 79  | 76  | 73  | 71  |    |    |   |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  | 78  | 73  | 69  | 76  | 72  | 69  | 75  | 71  | 68  | 67  |    |    |   |
| 7   | 85  | 76  | 70  | 66  | 83  | 75  | 69  | 66  | 74  | 69  | 65  | 73  | 68  | 65  | 71  | 67  | 64  | 63  |    |    |   |
| 8   | 81  | 72  | 66  | 62  | 80  | 71  | 66  | 62  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 60  |    |    |   |
| 9   | 77  | 68  | 62  | 58  | 76  | 67  | 62  | 58  | 66  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 58  | 56  |    |    |   |
| 10  | 74  | 65  | 59  | 55  | 73  | 64  | 59  | 55  | 63  | 58  | 55  | 63  | 58  | 55  | 62  | 58  | 55  | 53  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 212012 |
| 5°  | 205182 |
| 10° | 179075 |
| 15° | 147188 |
| 20° | 114678 |
| 25° | 87459  |
| 30° | 63333  |
| 35° | 43250  |
| 40° | 26979  |
| 45° | 16054  |
| 50° | 6362   |
| 55° | 4156   |
| 60° | 2952   |
| 65° | 1887   |
| 70° | 1662   |
| 75° | 1769   |
| 80° | 1955   |
| 85° | 2627   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16054 cd/sqm



TEST NUMBER: P642465

CATALOG NUMBER: ML5615LSFL409FS1E - 593WB - 1200LM - 5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 235.5  | 14.4      |
| 10°-20°   | 497.2  | 30.4      |
| 20°-30°   | 459.5  | 28.1      |
| 30°-40°   | 284.0  | 17.4      |
| 40°-50°   | 110.2  | 6.7       |
| 50°-60°   | 28.3   | 1.7       |
| 60°-70°   | 11.0   | 0.7       |
| 70°-80°   | 5.7    | 0.3       |
| 80°-90°   | 2.5    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1192.2 | 73.0      |
| 0°-40°    | 1476.3 | 90.3      |
| 0°-60°    | 1614.7 | 98.8      |
| 0°-90°    | 1634.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1634.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2686 |      |
| 5°  | 2589 | 235  |
| 15° | 1801 | 497  |
| 25° | 1004 | 460  |
| 35° | 449  | 284  |
| 45° | 144  | 110  |
| 55° | 30   | 28   |
| 65° | 10   | 11   |
| 75° | 6    | 6    |
| 85° | 3    | 3    |
| 90° | 0    |      |



TEST NUMBER: P642465

CATALOG NUMBER: ML5615LSFL409FS1E - 593WB - 1200LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2685.7 |
| 2.5°  | 2668.4 |
| 5°    | 2589.3 |
| 7.5°  | 2435.4 |
| 10°   | 2234.0 |
| 12.5° | 2015.3 |
| 15°   | 1801.0 |
| 17.5° | 1578.0 |
| 20°   | 1365.1 |
| 22.5° | 1173.8 |
| 25°   | 1004.1 |
| 27.5° | 841.5  |
| 30°   | 694.8  |
| 32.5° | 562.5  |
| 35°   | 448.8  |
| 37.5° | 352.4  |
| 40°   | 261.8  |
| 42.5° | 200.0  |
| 45°   | 143.8  |
| 47.5° | 80.6   |
| 50°   | 51.8   |
| 52.5° | 38.8   |
| 55°   | 30.2   |
| 57.5° | 23.0   |
| 60°   | 18.7   |
| 62.5° | 14.4   |
| 65°   | 10.1   |
| 67.5° | 7.2    |
| 70°   | 7.2    |
| 72.5° | 5.8    |
| 75°   | 5.8    |
| 77.5° | 4.3    |
| 80°   | 4.3    |
| 82.5° | 2.9    |
| 85°   | 2.9    |
| 87.5° | 1.4    |
| 90°   | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)