

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641980

Luminaire Tested: ML5612LSWFL5597FS1E - 592W - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-50)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 592W - 900LM - 5000K
Description: ML56 RR, 55D TIR OPTIC, 5" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1392.1 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641980
CATALOG NUMBER: ML5612LSWFL5597FS1E - 592W - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P641980
 CATALOG NUMBER: ML5612LSWFL5597FS1E - 592W - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93																			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79																			
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	72																			
5	90	81	75	71	89	81	75	70	79	74	70	77	73	69	75	72	68	67																			
6	85	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62																			
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58																			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54																			
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50																			
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116856
5°	111993
10°	106226
15°	99991
20°	90476
25°	77059
30°	62887
35°	49148
40°	35800
45°	22160
50°	8081
55°	4267
60°	2147
65°	1625
70°	1708
75°	1525
80°	1682
85°	1087

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22160 cd/sqm



TEST NUMBER: P641980

CATALOG NUMBER: ML5612LSWFL5597FS1E - 592W - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.2	9.5
10°-20°	340.7	24.5
20°-30°	404.0	29.0
30°-40°	318.1	22.8
40°-50°	149.8	10.8
50°-60°	30.5	2.2
60°-70°	9.3	0.7
70°-80°	5.7	0.4
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	876.9	63.0
0°-40°	1195.0	85.8
0°-60°	1375.2	98.8
0°-90°	1392.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1392.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1480	
5°	1413	132
15°	1224	341
25°	885	404
35°	510	318
45°	198	150
55°	31	30
65°	9	9
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P641980

CATALOG NUMBER: ML5612LSWFL5597FS1E - 592W - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1480.3
2.5°	1461.7
5°	1413.3
7.5°	1366.2
10°	1325.2
12.5°	1278.1
15°	1223.5
17.5°	1155.2
20°	1077.0
22.5°	985.2
25°	884.7
27.5°	784.2
30°	689.9
32.5°	599.3
35°	510.0
37.5°	424.4
40°	347.4
42.5°	273.0
45°	198.5
47.5°	111.7
50°	65.8
52.5°	44.7
55°	31.0
57.5°	22.3
60°	13.6
62.5°	11.2
65°	8.7
67.5°	7.4
70°	7.4
72.5°	6.2
75°	5.0
77.5°	5.0
80°	3.7
82.5°	2.5
85°	1.2
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)