

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642479

Luminaire Tested: ML5615LSFL409FS1E - 594SNB - 1200LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642479
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-33)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 594SNB - 1200LM - 4000K
Description: ML56 RR, 40D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1650.6 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642479

CATALOG NUMBER: ML5615LSFL409FS1E - 594SNB - 1200LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P642479

CATALOG NUMBER: ML5615LSFL409FS1E - 594SNB - 1200LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																											
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																											
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81																											
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																											
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	79	75	72	71																											
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																											
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																											
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																											
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																											
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	211230
5°	204636
10°	178089
15°	146215
20°	114443
25°	86614
30°	62221
35°	42239
40°	27246
45°	17650
50°	10230
55°	5739
60°	3852
65°	2690
70°	1985
75°	1739
80°	1318
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17650 cd/sqm



TEST NUMBER: P642479

CATALOG NUMBER: ML5615LSFL409FS1E - 594SNB - 1200LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.5	14.2
10°-20°	494.7	30.0
20°-30°	455.4	27.6
30°-40°	278.5	16.9
40°-50°	124.4	7.5
50°-60°	41.2	2.5
60°-70°	15.4	0.9
70°-80°	5.7	0.3
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1184.6	71.8
0°-40°	1463.1	88.6
0°-60°	1628.7	98.7
0°-90°	1650.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1650.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2676	
5°	2582	235
15°	1789	495
25°	994	455
35°	438	278
45°	158	124
55°	42	41
65°	14	15
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P642479

CATALOG NUMBER: ML5615LSFL409FS1E - 594SNB - 1200LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2675.8
2.5°	2660.0
5°	2582.4
7.5°	2424.3
10°	2221.7
12.5°	2004.7
15°	1789.1
17.5°	1570.7
20°	1362.3
22.5°	1166.9
25°	994.4
27.5°	830.6
30°	682.6
32.5°	550.4
35°	438.3
37.5°	343.5
40°	264.4
42.5°	204.1
45°	158.1
47.5°	116.4
50°	83.3
52.5°	58.9
55°	41.7
57.5°	31.6
60°	24.4
62.5°	20.1
65°	14.4
67.5°	11.5
70°	8.6
72.5°	7.2
75°	5.7
77.5°	2.9
80°	2.9
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)