

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641984

Luminaire Tested: ML5612LSWFL5597FS1E - 593BB - 1200LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641984
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 593BB - 1200LM - 4000K
Description: ML56 RR, 55D TIR OPTIC, 5" BLACK BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1632.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641984
CATALOG NUMBER: ML5612LSWFL5597FS1E - 593BB - 1200LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641984

CATALOG NUMBER: ML5612LSWFL5597FS1E - 593BB - 1200LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	83	81	79																			
4	96	88	83	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73																			
5	91	82	76	72	89	81	76	71	80	75	71	78	74	70	76	73	70	68																			
6	86	77	71	66	85	76	70	66	75	69	65	73	69	65	72	68	65	63																			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																			
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																			
9	74	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51																			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140341
5°	134332
10°	127340
15°	120014
20°	108604
25°	92336
30°	75138
35°	58457
40°	42086
45°	25811
50°	8486
55°	3716
60°	947
65°	280
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25811 cd/sqm



TEST NUMBER: P641984

CATALOG NUMBER: ML5612LSWFL5597FS1E - 593BB - 1200LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.5	9.7
10°-20°	408.9	25.1
20°-30°	484.3	29.7
30°-40°	378.2	23.2
40°-50°	172.9	10.6
50°-60°	27.4	1.7
60°-70°	1.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1051.7	64.4
0°-40°	1429.9	87.6
0°-60°	1630.2	99.9
0°-90°	1632.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1632.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1778	
5°	1695	159
15°	1468	409
25°	1060	484
35°	607	378
45°	231	173
55°	27	27
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641984

CATALOG NUMBER: ML5612LSWFL5597FS1E - 593BB - 1200LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1777.8
2.5°	1755.3
5°	1695.2
7.5°	1638.2
10°	1588.6
12.5°	1533.1
15°	1468.5
17.5°	1387.4
20°	1292.8
22.5°	1181.7
25°	1060.1
27.5°	940.0
30°	824.3
32.5°	713.2
35°	606.6
37.5°	504.5
40°	408.4
42.5°	319.8
45°	231.2
47.5°	123.1
50°	69.1
52.5°	43.5
55°	27.0
57.5°	16.5
60°	6.0
62.5°	3.0
65°	1.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)