

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642496

Luminaire Tested: ML5615LSFL409FS1E - 594TBZB - 1500LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642496
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-34)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 594TBZB - 1500LM - 2700K
Description: ML56 RR, 40D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1778.8 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642496
CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 1500LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642496

CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 1500LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81																			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	55	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	227666
5°	220524
10°	191924
15°	157681
20°	123028
25°	93443
30°	67317
35°	45399
40°	29318
45°	18923
50°	11077
55°	6207
60°	4168
65°	2895
70°	2147
75°	1891
80°	727
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18923 cd/sqm



TEST NUMBER: P642496

CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 1500LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.9	14.2
10°-20°	533.1	30.0
20°-30°	491.0	27.6
30°-40°	300.2	16.9
40°-50°	134.2	7.5
50°-60°	44.2	2.5
60°-70°	16.6	0.9
70°-80°	5.9	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1277.0	71.8
0°-40°	1577.2	88.7
0°-60°	1755.6	98.7
0°-90°	1778.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1778.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2884	
5°	2783	253
15°	1929	533
25°	1073	491
35°	471	300
45°	170	134
55°	45	44
65°	16	17
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P642496

CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 1500LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2884.0
2.5°	2865.3
5°	2782.9
7.5°	2616.6
10°	2394.3
12.5°	2161.1
15°	1929.4
17.5°	1693.1
20°	1464.5
22.5°	1256.2
25°	1072.8
27.5°	897.1
30°	738.5
32.5°	593.9
35°	471.1
37.5°	370.0
40°	284.5
42.5°	220.8
45°	169.5
47.5°	125.9
50°	90.2
52.5°	63.7
55°	45.1
57.5°	32.6
60°	26.4
62.5°	21.8
65°	15.5
67.5°	12.4
70°	9.3
72.5°	7.8
75°	6.2
77.5°	3.1
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)