

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641986

Luminaire Tested: ML5612LSWFL5597FS1E - 593BB - 600LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641986  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-52)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSWFL5597FS1E - 593BB - 600LM - 2700K  
Description: ML56 RR, 55D TIR OPTIC, 5" BLACK BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 924.4 lumens  
Efficiency: N/A  
Efficacy: 89.7 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641986  
CATALOG NUMBER: ML5612LSWFL5597FS1E - 593BB - 600LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P641986  
 CATALOG NUMBER: ML5612LSWFL5597FS1E - 593BB - 600LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	83	81	79																			
4	96	88	83	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73																			
5	91	82	76	72	89	81	76	71	80	75	71	78	74	70	76	73	70	68																			
6	86	77	71	66	85	76	70	66	75	69	65	73	69	65	72	68	65	63																			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																			
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																			
9	74	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51																			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	79486
5°	76081
10°	72127
15°	67971
20°	61510
25°	52296
30°	42559
35°	33112
40°	23835
45°	14625
50°	4802
55°	2106
60°	537
65°	168
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14625 cd/sqm



TEST NUMBER: P641986

CATALOG NUMBER: ML5612LSWFL5597FS1E - 593BB - 600LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.8	9.7
10°-20°	231.6	25.1
20°-30°	274.3	29.7
30°-40°	214.2	23.2
40°-50°	97.9	10.6
50°-60°	15.6	1.7
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	595.6	64.4
0°-40°	809.9	87.6
0°-60°	923.3	99.9
0°-90°	924.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	924.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1007	
5°	960	90
15°	832	232
25°	600	274
35°	344	214
45°	131	98
55°	15	16
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641986

CATALOG NUMBER: ML5612LSWFL5597FS1E - 593BB - 600LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1006.9
2.5°	994.2
5°	960.1
7.5°	927.8
10°	899.8
12.5°	868.3
15°	831.7
17.5°	785.8
20°	732.2
22.5°	669.3
25°	600.4
27.5°	532.4
30°	466.9
32.5°	404.0
35°	343.6
37.5°	285.7
40°	231.3
42.5°	181.1
45°	131.0
47.5°	69.7
50°	39.1
52.5°	24.7
55°	15.3
57.5°	9.4
60°	3.4
62.5°	1.7
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)