

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642503

Luminaire Tested: ML5615LSFL409FS1E - 594TBZB - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-34)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 594TBZB - 900LM - 3500K
Description: ML56 RR, 40D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1208.8 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642503

CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642503

CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81																			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	55	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	154701
5°	149847
10°	130410
15°	107142
20°	83604
25°	63488
30°	45741
35°	30848
40°	19920
45°	12861
50°	7528
55°	4211
60°	2842
65°	1980
70°	1454
75°	1281
80°	500
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12861 cd/sqm



TEST NUMBER: P642503

CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.8	14.2
10°-20°	362.3	30.0
20°-30°	333.6	27.6
30°-40°	204.0	16.9
40°-50°	91.2	7.5
50°-60°	30.1	2.5
60°-70°	11.4	0.9
70°-80°	4.0	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	867.7	71.8
0°-40°	1071.7	88.7
0°-60°	1192.9	98.7
0°-90°	1208.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1208.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1960	
5°	1891	172
15°	1311	362
25°	729	334
35°	320	204
45°	115	91
55°	31	30
65°	11	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P642503

CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1959.7
2.5°	1947.0
5°	1891.0
7.5°	1778.0
10°	1626.9
12.5°	1468.4
15°	1311.0
17.5°	1150.5
20°	995.2
22.5°	853.6
25°	728.9
27.5°	609.6
30°	501.8
32.5°	403.6
35°	320.1
37.5°	251.4
40°	193.3
42.5°	150.0
45°	115.2
47.5°	85.6
50°	61.3
52.5°	43.3
55°	30.6
57.5°	22.2
60°	18.0
62.5°	14.8
65°	10.6
67.5°	8.5
70°	6.3
72.5°	5.3
75°	4.2
77.5°	2.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)