

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642514

Luminaire Tested: ML5615LSFL409FS1E - 594WB - 1500LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-32)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 594WB - 1500LM - 4000K
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2031.1 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642514
CATALOG NUMBER: ML5615LSFL409FS1E - 594WB - 1500LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P642514

CATALOG NUMBER: ML5615LSFL409FS1E - 594WB - 1500LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	86	84	87	85	83	81																			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	260000
5°	251745
10°	218945
15°	180025
20°	140645
25°	106560
30°	76386
35°	51962
40°	33522
45°	21513
50°	12588
55°	7060
60°	4752
65°	3306
70°	2862
75°	2166
80°	1591
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21513 cd/sqm



TEST NUMBER: P642514

CATALOG NUMBER: ML5615LSFL409FS1E - 594WB - 1500LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	288.4	14.2
10°-20°	608.6	30.0
20°-30°	560.0	27.6
30°-40°	342.5	16.9
40°-50°	153.0	7.5
50°-60°	50.8	2.5
60°-70°	19.2	0.9
70°-80°	7.7	0.4
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1457.0	71.7
0°-40°	1799.4	88.6
0°-60°	2003.2	98.6
0°-90°	2031.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2031.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3294	
5°	3177	288
15°	2203	609
25°	1223	560
35°	539	342
45°	193	153
55°	51	51
65°	18	19
75°	7	8
85°	0	1
90°	0	



TEST NUMBER: P642514

CATALOG NUMBER: ML5615LSFL409FS1E - 594WB - 1500LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3293.6
2.5°	3272.4
5°	3176.9
7.5°	2980.6
10°	2731.4
12.5°	2468.0
15°	2202.8
17.5°	1930.5
20°	1674.2
22.5°	1435.5
25°	1223.4
27.5°	1021.8
30°	838.0
32.5°	677.1
35°	539.2
37.5°	422.5
40°	325.3
42.5°	252.8
45°	192.7
47.5°	143.2
50°	102.5
52.5°	72.5
55°	51.3
57.5°	38.9
60°	30.1
62.5°	24.8
65°	17.7
67.5°	14.1
70°	12.4
72.5°	8.8
75°	7.1
77.5°	5.3
80°	3.5
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)