

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642033

Luminaire Tested: ML5612LSWFL5597FS1E - 593WB - 600LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642033
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-51)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 593WB - 600LM - 3500K
Description: ML56 RR, 55D TIR OPTIC, 5" WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1007.3 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642033
CATALOG NUMBER: ML5612LSWFL5597FS1E - 593WB - 600LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642033

CATALOG NUMBER: ML5612LSWFL5597FS1E - 593WB - 600LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93																
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85																
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79																
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	72			72																
5	90	81	75	71	89	81	75	70	79	74	70	77	73	69	75	72	68	67			67																
6	85	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62																
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58																
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54																
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50																
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84546
5°	80954
10°	76776
15°	72327
20°	65442
25°	55797
30°	45540
35°	35676
40°	25835
45°	16054
50°	5735
55°	3097
60°	1563
65°	1177
70°	1246
75°	1098
80°	1227
85°	1630

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16054 cd/sqm



TEST NUMBER: P642033

CATALOG NUMBER: ML5612LSWFL5597FS1E - 593WB - 600LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.6	9.5
10°-20°	246.4	24.5
20°-30°	292.5	29.0
30°-40°	230.4	22.9
40°-50°	108.3	10.7
50°-60°	21.8	2.2
60°-70°	6.6	0.7
70°-80°	4.2	0.4
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	634.5	63.0
0°-40°	864.9	85.9
0°-60°	995.0	98.8
0°-90°	1007.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1007.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1071	
5°	1022	96
15°	885	246
25°	641	293
35°	370	230
45°	144	108
55°	22	22
65°	6	7
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P642033

CATALOG NUMBER: ML5612LSWFL5597FS1E - 593WB - 600LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1071.0
2.5°	1057.5
5°	1021.6
7.5°	988.3
10°	957.8
12.5°	924.6
15°	885.0
17.5°	835.6
20°	779.0
22.5°	713.4
25°	640.6
27.5°	567.9
30°	499.6
32.5°	434.0
35°	370.2
37.5°	307.3
40°	250.7
42.5°	198.6
45°	143.8
47.5°	80.0
50°	46.7
52.5°	32.3
55°	22.5
57.5°	15.3
60°	9.9
62.5°	7.2
65°	6.3
67.5°	5.4
70°	5.4
72.5°	4.5
75°	3.6
77.5°	3.6
80°	2.7
82.5°	1.8
85°	1.8
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)