

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642520

Luminaire Tested: ML5615LSFL409FS1E - 594WB - 900LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642520  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-32)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSFL409FS1E - 594WB - 900LM - 5000K  
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE GIMBAL TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1306.7 lumens  
Efficiency: N/A  
Efficacy: 124.4 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642520  
CATALOG NUMBER: ML5615LSFL409FS1E - 594WB - 900LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642520

CATALOG NUMBER: ML5615LSFL409FS1E - 594WB - 900LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	86	84	87	85	83	81																			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	167276
5°	161964
10°	140863
15°	115822
20°	90484
25°	68558
30°	49141
35°	33430
40°	21568
45°	13843
50°	8105
55°	4542
60°	3047
65°	2129
70°	1846
75°	1373
80°	1046
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13843 cd/sqm



TEST NUMBER: P642520

CATALOG NUMBER: ML5615LSFL409FS1E - 594WB - 900LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	185.6	14.2
10°-20°	391.5	30.0
20°-30°	360.3	27.6
30°-40°	220.3	16.9
40°-50°	98.5	7.5
50°-60°	32.6	2.5
60°-70°	12.3	0.9
70°-80°	4.9	0.4
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	937.4	71.7
0°-40°	1157.7	88.6
0°-60°	1288.8	98.6
0°-90°	1306.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1306.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2119	
5°	2044	186
15°	1417	392
25°	787	360
35°	347	220
45°	124	98
55°	33	33
65°	11	12
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P642520  
CATALOG NUMBER: ML5615LSFL409FS1E - 594WB - 900LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2119.0
2.5°	2105.3
5°	2043.9
7.5°	1917.6
10°	1757.3
12.5°	1587.8
15°	1417.2
17.5°	1242.0
20°	1077.1
22.5°	923.6
25°	787.1
27.5°	657.4
30°	539.1
32.5°	435.6
35°	346.9
37.5°	271.8
40°	209.3
42.5°	162.6
45°	124.0
47.5°	92.1
50°	66.0
52.5°	46.6
55°	33.0
57.5°	25.0
60°	19.3
62.5°	15.9
65°	11.4
67.5°	9.1
70°	8.0
72.5°	5.7
75°	4.5
77.5°	3.4
80°	2.3
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)