

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: HALO

Report Number: P642038

Luminaire Tested: ML5612LSWFL5597FS1E - 593WB - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-51)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 593WB - 900LM - 3500K
Description: ML56 RR, 55D TIR OPTIC, 5" WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1292.2 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642038
CATALOG NUMBER: ML5612LSWFL5597FS1E - 593WB - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642038

CATALOG NUMBER: ML5612LSWFL5597FS1E - 593WB - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93																
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85																
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			79																
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	72			72																
5	90	81	75	71	89	81	75	70	79	74	70	77	73	69	75	72	68	67			67																
6	85	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62																
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58																
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54																
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50																
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108473
5°	103863
10°	98499
15°	92799
20°	83957
25°	71589
30°	58420
35°	45766
40°	33141
45°	20586
50°	7356
55°	3964
60°	2005
65°	1513
70°	1593
75°	1403
80°	1591
85°	2083

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20586 cd/sqm



TEST NUMBER: P642038

CATALOG NUMBER: ML5612LSWFL5597FS1E - 593WB - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.6	9.5
10°-20°	316.2	24.5
20°-30°	375.3	29.0
30°-40°	295.6	22.9
40°-50°	138.9	10.7
50°-60°	27.9	2.2
60°-70°	8.4	0.7
70°-80°	5.3	0.4
80°-90°	2.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.1	63.0
0°-40°	1109.6	85.9
0°-60°	1276.4	98.8
0°-90°	1292.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1292.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1374	
5°	1311	123
15°	1136	316
25°	822	375
35°	475	296
45°	184	139
55°	29	28
65°	8	8
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P642038

CATALOG NUMBER: ML5612LSWFL5597FS1E - 593WB - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1374.1
2.5°	1356.8
5°	1310.7
7.5°	1268.0
10°	1228.8
12.5°	1186.2
15°	1135.5
17.5°	1072.1
20°	999.4
22.5°	915.3
25°	821.9
27.5°	728.5
30°	640.9
32.5°	556.8
35°	474.9
37.5°	394.2
40°	321.6
42.5°	254.8
45°	184.4
47.5°	102.6
50°	59.9
52.5°	41.5
55°	28.8
57.5°	19.6
60°	12.7
62.5°	9.2
65°	8.1
67.5°	6.9
70°	6.9
72.5°	5.8
75°	4.6
77.5°	4.6
80°	3.5
82.5°	2.3
85°	2.3
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)