

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642046

Luminaire Tested: ML5612LSWFL5597FS1E - 594SNB - 600LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642046
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-56)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 594SNB - 600LM - 2700K
Description: ML56 RR, 55D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 968.7 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642046

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594SNB - 600LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642046

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594SNB - 600LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98 | 97 | 97 | 95 | 94 | 92 | | | 92 | | | | | | | | | | | | | | | | |
| 2 | 107 | 101 | 97 | 93 | 105 | 100 | 96 | 92 | 96 | 93 | 90 | 93 | 91 | 88 | 91 | 88 | 87 | 85 | | | 85 | | | | | | | | | | | | | | | | |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 87 | 83 | 90 | 86 | 82 | 87 | 84 | 81 | 85 | 82 | 80 | 78 | | | 78 | | | | | | | | | | | | | | | | |
| 4 | 95 | 87 | 81 | 76 | 93 | 86 | 80 | 76 | 84 | 79 | 75 | 82 | 77 | 74 | 80 | 76 | 73 | 72 | | | 72 | | | | | | | | | | | | | | | | |
| 5 | 90 | 81 | 74 | 70 | 88 | 80 | 74 | 69 | 78 | 73 | 69 | 76 | 72 | 68 | 75 | 71 | 68 | 66 | | | 66 | | | | | | | | | | | | | | | | |
| 6 | 85 | 75 | 69 | 64 | 83 | 74 | 68 | 64 | 73 | 68 | 64 | 71 | 67 | 63 | 70 | 66 | 63 | 61 | | | 61 | | | | | | | | | | | | | | | | |
| 7 | 80 | 70 | 64 | 59 | 79 | 70 | 64 | 59 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 58 | 57 | | | 57 | | | | | | | | | | | | | | | | |
| 8 | 76 | 66 | 59 | 55 | 75 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 54 | 62 | 58 | 54 | 53 | | | 53 | | | | | | | | | | | | | | | | |
| 9 | 72 | 62 | 56 | 51 | 71 | 61 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 51 | 59 | 54 | 51 | 49 | | | 49 | | | | | | | | | | | | | | | | |
| 10 | 69 | 58 | 52 | 48 | 68 | 58 | 52 | 48 | 57 | 52 | 48 | 56 | 51 | 48 | 55 | 51 | 47 | 46 | | | 46 | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 79628 |
| 5° | 76287 |
| 10° | 72399 |
| 15° | 68462 |
| 20° | 61947 |
| 25° | 52296 |
| 30° | 42404 |
| 35° | 32949 |
| 40° | 24361 |
| 45° | 15953 |
| 50° | 7627 |
| 55° | 4101 |
| 60° | 2684 |
| 65° | 2223 |
| 70° | 1962 |
| 75° | 1312 |
| 80° | 773 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15953 cd/sqm



TEST NUMBER: P642046

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594SNB - 600LM - 2700K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 90.0 | 9.3 |
| 10°-20° | 233.1 | 24.1 |
| 20°-30° | 274.8 | 28.4 |
| 30°-40° | 214.2 | 22.1 |
| 40°-50° | 109.5 | 11.3 |
| 50°-60° | 29.7 | 3.1 |
| 60°-70° | 12.2 | 1.3 |
| 70°-80° | 4.7 | 0.5 |
| 80°-90° | 0.5 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 597.9 | 61.7 |
| 0°-40° | 812.1 | 83.8 |
| 0°-60° | 951.3 | 98.2 |
| 0°-90° | 968.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 968.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1009 | |
| 5° | 963 | 90 |
| 15° | 838 | 233 |
| 25° | 600 | 275 |
| 35° | 342 | 214 |
| 45° | 143 | 110 |
| 55° | 30 | 30 |
| 65° | 12 | 12 |
| 75° | 4 | 5 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P642046

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594SNB - 600LM - 2700K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1008.7 |
| 2.5° | 995.9 |
| 5° | 962.7 |
| 7.5° | 930.4 |
| 10° | 903.2 |
| 12.5° | 873.4 |
| 15° | 837.7 |
| 17.5° | 791.8 |
| 20° | 737.4 |
| 22.5° | 673.6 |
| 25° | 600.4 |
| 27.5° | 531.5 |
| 30° | 465.2 |
| 32.5° | 402.3 |
| 35° | 341.9 |
| 37.5° | 286.6 |
| 40° | 236.4 |
| 42.5° | 188.0 |
| 45° | 142.9 |
| 47.5° | 95.3 |
| 50° | 62.1 |
| 52.5° | 42.5 |
| 55° | 29.8 |
| 57.5° | 22.1 |
| 60° | 17.0 |
| 62.5° | 14.5 |
| 65° | 11.9 |
| 67.5° | 10.2 |
| 70° | 8.5 |
| 72.5° | 6.0 |
| 75° | 4.3 |
| 77.5° | 2.6 |
| 80° | 1.7 |
| 82.5° | 0.9 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)