

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642585

Luminaire Tested: ML5615LSFL409FS1E - 692W - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642585
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-39)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 692W - 1200LM - 5000K
Description: ML56 RR, 40D TIR OPTIC, 6" WHITE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1646.8 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642585
CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642585
 CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	98	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	78	76																			
5	93	85	79	75	91	84	79	75	82	78	74	81	76	73	79	75	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63																			
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56																			
10	74	64	59	55	73	64	58	55	63	58	55	62	58	55	62	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147121
5°	142620
10°	124263
15°	102055
20°	79667
25°	60602
30°	43950
35°	30109
40°	19544
45°	12149
50°	6371
55°	2886
60°	1886
65°	1116
70°	689
75°	614
80°	916
85°	881

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12149 cd/sqm



TEST NUMBER: P642585

CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.5	14.3
10°-20°	496.6	30.2
20°-30°	459.3	27.9
30°-40°	285.5	17.3
40°-50°	125.4	7.6
50°-60°	30.8	1.9
60°-70°	9.0	0.5
70°-80°	3.6	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1191.4	72.3
0°-40°	1476.9	89.7
0°-60°	1633.1	99.2
0°-90°	1646.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1646.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2684	
5°	2592	235
15°	1798	497
25°	1002	459
35°	450	285
45°	157	125
55°	30	31
65°	9	9
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P642585

CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2683.7
2.5°	2666.4
5°	2591.7
7.5°	2435.0
10°	2232.3
12.5°	2016.7
15°	1798.2
17.5°	1572.5
20°	1365.6
22.5°	1172.9
25°	1001.9
27.5°	842.3
30°	694.3
32.5°	563.5
35°	449.9
37.5°	353.6
40°	273.1
42.5°	211.3
45°	156.7
47.5°	116.4
50°	74.7
52.5°	40.2
55°	30.2
57.5°	23.0
60°	17.2
62.5°	12.9
65°	8.6
67.5°	4.3
70°	4.3
72.5°	4.3
75°	2.9
77.5°	2.9
80°	2.9
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)