

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642066

Luminaire Tested: ML5612LSWFL5597FS1E - 594TBZB - 900LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642066
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 594TBZB - 900LM - 2700K
Description: ML56 RR, 55D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1240.5 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642066

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 900LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642066

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 900LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			92																
2	107	101	97	93	105	100	96	92	96	93	90	93	91	88	91	88	87	85			85																
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78																
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72																
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66																
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61			61																
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57																
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53			53																
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49			49																
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	47	46			46																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	101992
5°	97627
10°	92631
15°	87577
20°	79294
25°	67103
30°	54409
35°	42277
40°	31152
45°	20463
50°	9923
55°	5257
60°	3442
65°	2858
70°	2262
75°	1678
80°	1000
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20463 cd/sqm



TEST NUMBER: P642066

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 900LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.3	9.3
10°-20°	298.3	24.0
20°-30°	352.1	28.4
30°-40°	274.4	22.1
40°-50°	140.3	11.3
50°-60°	38.2	3.1
60°-70°	15.5	1.3
70°-80°	5.9	0.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	765.7	61.7
0°-40°	1040.0	83.8
0°-60°	1218.5	98.2
0°-90°	1240.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1240.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1292	
5°	1232	115
15°	1072	298
25°	770	352
35°	439	274
45°	183	140
55°	38	38
65°	15	16
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P642066

CATALOG NUMBER: ML5612LSWFL5597FS1E - 594TBZB - 900LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1292.0
2.5°	1275.7
5°	1232.0
7.5°	1191.6
10°	1155.6
12.5°	1117.4
15°	1071.6
17.5°	1013.8
20°	943.9
22.5°	862.1
25°	770.4
27.5°	680.9
30°	596.9
32.5°	515.1
35°	438.7
37.5°	366.7
40°	302.3
42.5°	241.2
45°	183.3
47.5°	121.1
50°	80.8
52.5°	54.6
55°	38.2
57.5°	28.4
60°	21.8
62.5°	18.6
65°	15.3
67.5°	13.1
70°	9.8
72.5°	7.6
75°	5.5
77.5°	3.3
80°	2.2
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)