

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642591

Luminaire Tested: ML5615LSFL409FS1E - 692W - 900LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642591  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-39)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSFL409FS1E - 692W - 900LM - 2700K  
Description: ML56 RR, 40D TIR OPTIC, 6" WHITE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1145.0 lumens  
Efficiency: N/A  
Efficacy: 109.0 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642591  
CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 900LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P642591

CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 900LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	98	96	95	94			94																
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			87																
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81			81																
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	78	76			76																
5	93	85	79	75	91	84	79	75	82	78	74	80	76	73	79	75	73	71			71																
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67																
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			63																
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59			59																
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56			56																
10	74	64	59	55	73	64	58	55	63	58	55	62	58	55	62	57	54	53			53																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	102283
5°	99152
10°	86393
15°	70954
20°	55386
25°	42135
30°	30555
35°	20934
40°	13590
45°	8443
50°	4435
55°	2007
60°	1316
65°	778
70°	481
75°	424
80°	631
85°	629

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8443 cd/sqm



TEST NUMBER: P642591

CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 900LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.7	14.3
10°-20°	345.3	30.2
20°-30°	319.3	27.9
30°-40°	198.5	17.3
40°-50°	87.2	7.6
50°-60°	21.5	1.9
60°-70°	6.3	0.5
70°-80°	2.5	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	828.3	72.3
0°-40°	1026.8	89.7
0°-60°	1135.4	99.2
0°-90°	1145.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1145.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1866	
5°	1802	164
15°	1250	345
25°	697	319
35°	313	198
45°	109	87
55°	21	21
65°	6	6
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P642591

CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 900LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1865.8
2.5°	1853.8
5°	1801.8
7.5°	1692.9
10°	1552.0
12.5°	1402.1
15°	1250.2
17.5°	1093.3
20°	949.4
22.5°	815.5
25°	696.6
27.5°	585.6
30°	482.7
32.5°	391.7
35°	312.8
37.5°	245.8
40°	189.9
42.5°	146.9
45°	108.9
47.5°	80.9
50°	52.0
52.5°	28.0
55°	21.0
57.5°	16.0
60°	12.0
62.5°	9.0
65°	6.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	2.0
77.5°	2.0
80°	2.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)