

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642599

Luminaire Tested: ML5615LSFL409FS1E - 693BB - 1200LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642599
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-41)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 693BB - 1200LM - 4000K
Description: ML56 RR, 40D TIR OPTIC, 6" BLACK BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1618.9 lumens
Efficiency: N/A
Efficacy: 120.8 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642599
CATALOG NUMBER: ML5615LSFL409FS1E - 693BB - 1200LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P642599

CATALOG NUMBER: ML5615LSFL409FS1E - 693BB - 1200LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82																			
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77																			
5	93	85	80	76	92	84	79	75	83	78	75	81	77	74	79	76	73	72																			
6	89	80	75	70	88	80	74	70	78	73	70	77	73	69	75	72	69	67																			
7	85	76	70	66	84	75	70	66	74	69	66	73	68	65	72	68	65	63																			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60																			
9	77	68	62	59	76	68	62	59	67	62	58	66	61	58	65	61	58	57																			
10	74	65	59	55	73	64	59	55	64	59	55	63	58	55	62	58	55	54																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146326
5°	141740
10°	123606
15°	101374
20°	79200
25°	60197
30°	43697
35°	29741
40°	19143
45°	11707
50°	5885
55°	2332
60°	1414
65°	558
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11707 cd/sqm



TEST NUMBER: P642599

CATALOG NUMBER: ML5615LSFL409FS1E - 693BB - 1200LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.2	14.5
10°-20°	493.9	30.5
20°-30°	456.3	28.2
30°-40°	282.3	17.4
40°-50°	121.3	7.5
50°-60°	26.2	1.6
60°-70°	4.7	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1184.4	73.2
0°-40°	1466.8	90.6
0°-60°	1614.2	99.7
0°-90°	1618.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1618.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2669	
5°	2576	234
15°	1786	494
25°	995	456
35°	444	282
45°	151	121
55°	24	26
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642599

CATALOG NUMBER: ML5615LSFL409FS1E - 693BB - 1200LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2669.2
2.5°	2654.8
5°	2575.7
7.5°	2423.3
10°	2220.5
12.5°	2003.3
15°	1786.2
17.5°	1567.6
20°	1357.6
22.5°	1166.3
25°	995.2
27.5°	835.6
30°	690.3
32.5°	559.4
35°	444.4
37.5°	348.0
40°	267.5
42.5°	207.1
45°	151.0
47.5°	110.7
50°	69.0
52.5°	36.0
55°	24.4
57.5°	17.3
60°	12.9
62.5°	8.6
65°	4.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)