

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642128

Luminaire Tested: ML5612LSWFL5597FS1E - 692H - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-61)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 692H - 900LM - 3500K
Description: ML56 RR, 55D TIR OPTIC, 6" HAZE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1299.2 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642128

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642128

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86																			
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79																			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73																			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67																			
6	86	76	70	66	84	76	70	65	74	69	65	73	68	64	71	67	64	62																			
7	81	71	65	61	80	71	65	60	69	64	60	68	63	60	67	63	59	58																			
8	77	67	61	56	76	66	60	56	65	60	56	64	59	56	63	59	55	54																			
9	73	63	57	52	72	62	56	52	61	56	52	60	56	52	60	55	52	50																			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76375
5°	73239
10°	69143
15°	65063
20°	58805
25°	49950
30°	40734
35°	31802
40°	23523
45°	15288
50°	6294
55°	2428
60°	1140
65°	298
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15288 cd/sqm



TEST NUMBER: P642128

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	9.6
10°-20°	319.1	24.6
20°-30°	377.5	29.1
30°-40°	297.2	22.9
40°-50°	149.6	11.5
50°-60°	27.6	2.1
60°-70°	3.4	0.3
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	820.8	63.2
0°-40°	1118.1	86.1
0°-60°	1295.3	99.7
0°-90°	1299.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1299.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1393	
5°	1331	124
15°	1146	319
25°	826	377
35°	475	297
45°	197	150
55°	25	28
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642128

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692H - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1393.2
2.5°	1377.1
5°	1330.9
7.5°	1283.6
10°	1242.1
12.5°	1197.1
15°	1146.4
17.5°	1081.8
20°	1008.0
22.5°	921.5
25°	825.8
27.5°	732.4
30°	643.5
32.5°	558.2
35°	475.2
37.5°	397.9
40°	328.7
42.5°	260.6
45°	197.2
47.5°	128.0
50°	73.8
52.5°	40.4
55°	25.4
57.5°	17.3
60°	10.4
62.5°	4.6
65°	2.3
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)