

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642157

Luminaire Tested: ML5612LSWFL5597FS1E - 692W - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642157
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-62)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 692W - 900LM - 3000K
Description: ML56 RR, 55D TIR OPTIC, 6" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1268.1 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642157
CATALOG NUMBER: ML5612LSWFL5597FS1E - 692W - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P642157

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692W - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79																			
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72																			
5	90	81	75	71	89	80	75	70	79	73	70	77	72	69	75	71	68	67																			
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62																			
7	81	71	65	60	79	70	64	60	69	63	60	68	63	59	67	62	59	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	62	56	52	71	62	56	52	61	55	52	60	55	51	59	55	51	50																			
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73125
5°	70130
10°	66382
15°	62651
20°	56746
25°	48317
30°	39487
35°	30858
40°	22879
45°	14963
50°	6413
55°	2676
60°	1480
65°	869
70°	721
75°	720
80°	695
85°	692

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14963 cd/sqm



TEST NUMBER: P642157

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692W - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.1	9.4
10°-20°	307.3	24.2
20°-30°	364.9	28.8
30°-40°	288.8	22.8
40°-50°	146.8	11.6
50°-60°	29.8	2.4
60°-70°	7.2	0.6
70°-80°	3.3	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	791.3	62.4
0°-40°	1080.1	85.2
0°-60°	1256.8	99.1
0°-90°	1268.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1268.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1334	
5°	1274	119
15°	1104	307
25°	799	365
35°	461	289
45°	193	147
55°	28	30
65°	7	7
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P642157

CATALOG NUMBER: ML5612LSWFL5597FS1E - 692W - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1333.9
2.5°	1318.2
5°	1274.4
7.5°	1231.8
10°	1192.5
12.5°	1152.2
15°	1103.9
17.5°	1042.2
20°	972.7
22.5°	889.6
25°	798.8
27.5°	707.9
30°	623.8
32.5°	541.9
35°	461.1
37.5°	388.2
40°	319.7
42.5°	254.7
45°	193.0
47.5°	126.8
50°	75.2
52.5°	42.6
55°	28.0
57.5°	20.2
60°	13.5
62.5°	9.0
65°	6.7
67.5°	4.5
70°	4.5
72.5°	3.4
75°	3.4
77.5°	2.2
80°	2.2
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)