

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642217

Luminaire Tested: ML5612LSWFL5597FS1E - 693WB - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642217
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-63)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 693WB - 900LM - 3000K
Description: ML56 RR, 55D TIR OPTIC, 6" WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1267.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642217
CATALOG NUMBER: ML5612LSWFL5597FS1E - 693WB - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P642217

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693WB - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 94 | 93 | | | 93 | | | | | | | | | | | | | | | | |
| 2 | 107 | 102 | 98 | 94 | 105 | 100 | 96 | 93 | 97 | 94 | 91 | 94 | 91 | 89 | 91 | 89 | 87 | 85 | | | 85 | | | | | | | | | | | | | | | | |
| 3 | 101 | 94 | 89 | 85 | 99 | 93 | 88 | 84 | 90 | 86 | 83 | 88 | 84 | 81 | 85 | 83 | 80 | 78 | | | 78 | | | | | | | | | | | | | | | | |
| 4 | 96 | 87 | 82 | 77 | 94 | 86 | 81 | 77 | 84 | 79 | 76 | 82 | 78 | 75 | 80 | 77 | 74 | 72 | | | 72 | | | | | | | | | | | | | | | | |
| 5 | 90 | 81 | 75 | 71 | 89 | 80 | 75 | 70 | 79 | 73 | 70 | 77 | 72 | 69 | 75 | 71 | 68 | 67 | | | 67 | | | | | | | | | | | | | | | | |
| 6 | 85 | 76 | 69 | 65 | 84 | 75 | 69 | 65 | 73 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 63 | 62 | | | 62 | | | | | | | | | | | | | | | | |
| 7 | 81 | 71 | 64 | 60 | 79 | 70 | 64 | 60 | 69 | 63 | 59 | 68 | 63 | 59 | 66 | 62 | 59 | 57 | | | 57 | | | | | | | | | | | | | | | | |
| 8 | 77 | 66 | 60 | 56 | 75 | 66 | 60 | 56 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 55 | 53 | | | 53 | | | | | | | | | | | | | | | | |
| 9 | 73 | 62 | 56 | 52 | 71 | 62 | 56 | 52 | 61 | 55 | 52 | 60 | 55 | 51 | 59 | 55 | 51 | 50 | | | 50 | | | | | | | | | | | | | | | | |
| 10 | 69 | 59 | 53 | 49 | 68 | 58 | 52 | 48 | 57 | 52 | 48 | 57 | 52 | 48 | 56 | 51 | 48 | 47 | | | 47 | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 72944 |
| 5° | 69888 |
| 10° | 66326 |
| 15° | 62463 |
| 20° | 56617 |
| 25° | 48184 |
| 30° | 39417 |
| 35° | 30858 |
| 40° | 22886 |
| 45° | 15048 |
| 50° | 6507 |
| 55° | 2676 |
| 60° | 1480 |
| 65° | 726 |
| 70° | 721 |
| 75° | 720 |
| 80° | 695 |
| 85° | 692 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15048 cd/sqm



TEST NUMBER: P642217

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693WB - 900LM - 3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 118.8 | 9.4 |
| 10°-20° | 306.6 | 24.2 |
| 20°-30° | 364.2 | 28.7 |
| 30°-40° | 288.6 | 22.8 |
| 40°-50° | 147.2 | 11.6 |
| 50°-60° | 30.0 | 2.4 |
| 60°-70° | 6.6 | 0.5 |
| 70°-80° | 3.6 | 0.3 |
| 80°-90° | 1.5 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 789.5 | 62.3 |
| 0°-40° | 1078.1 | 85.1 |
| 0°-60° | 1255.3 | 99.1 |
| 0°-90° | 1267.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1267.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1331 | |
| 5° | 1270 | 119 |
| 15° | 1101 | 307 |
| 25° | 797 | 364 |
| 35° | 461 | 289 |
| 45° | 194 | 147 |
| 55° | 28 | 30 |
| 65° | 6 | 7 |
| 75° | 3 | 4 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P642217

CATALOG NUMBER: ML5612LSWFL5597FS1E - 693WB - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1330.6 |
| 2.5° | 1313.8 |
| 5° | 1270.0 |
| 7.5° | 1228.5 |
| 10° | 1191.5 |
| 12.5° | 1148.9 |
| 15° | 1100.6 |
| 17.5° | 1040.0 |
| 20° | 970.5 |
| 22.5° | 888.6 |
| 25° | 796.6 |
| 27.5° | 706.8 |
| 30° | 622.7 |
| 32.5° | 540.8 |
| 35° | 461.1 |
| 37.5° | 388.2 |
| 40° | 319.8 |
| 42.5° | 254.7 |
| 45° | 194.1 |
| 47.5° | 126.8 |
| 50° | 76.3 |
| 52.5° | 42.6 |
| 55° | 28.0 |
| 57.5° | 20.2 |
| 60° | 13.5 |
| 62.5° | 7.9 |
| 65° | 5.6 |
| 67.5° | 4.5 |
| 70° | 4.5 |
| 72.5° | 3.4 |
| 75° | 3.4 |
| 77.5° | 3.4 |
| 80° | 2.2 |
| 82.5° | 2.2 |
| 85° | 1.1 |
| 87.5° | 1.1 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)