

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642674

Luminaire Tested: ML5615LSFL409FS1E - 694WB - 1200LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642674  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSFL409FS1E - 694WB - 1200LM - 4000K  
Description: ML56 RR, 40D TIR OPTIC, 6" WHITE GIMBAL TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1654.9 lumens  
Efficiency: N/A  
Efficacy: 123.5 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642674

CATALOG NUMBER: ML5615LSFL409FS1E - 694WB - 1200LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642674

CATALOG NUMBER: ML5615LSFL409FS1E - 694WB - 1200LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93				93
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87				87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81				81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76				76
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71				71
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66				66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62				62
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59				59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56				56
10	73	64	58	55	72	63	58	54	63	58	54	62	57	54	61	57	54	53				53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	147110
5°	142367
10°	123923
15°	101777
20°	79451
25°	60282
30°	43329
35°	29453
40°	18935
45°	12265
50°	7113
55°	3986
60°	2675
65°	1868
70°	1378
75°	1228
80°	442
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12265 cd/sqm



TEST NUMBER: P642674

CATALOG NUMBER: ML5615LSFL409FS1E - 694WB - 1200LM - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	235.1	14.2
10°-20°	495.9	30.0
20°-30°	456.6	27.6
30°-40°	279.4	16.9
40°-50°	125.1	7.6
50°-60°	41.3	2.5
60°-70°	15.4	0.9
70°-80°	5.5	0.3
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1187.6	71.8
0°-40°	1467.1	88.7
0°-60°	1633.4	98.7
0°-90°	1654.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1654.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2684	
5°	2587	235
15°	1793	496
25°	997	457
35°	440	279
45°	158	125
55°	42	41
65°	14	15
75°	6	5
85°	0	1
90°	0	



TEST NUMBER: P642674

CATALOG NUMBER: ML5615LSFL409FS1E - 694WB - 1200LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2683.5
2.5°	2666.2
5°	2587.1
7.5°	2431.8
10°	2226.2
12.5°	2013.3
15°	1793.3
17.5°	1574.7
20°	1361.9
22.5°	1169.2
25°	996.6
27.5°	835.5
30°	684.5
32.5°	552.2
35°	440.1
37.5°	345.1
40°	264.6
42.5°	207.1
45°	158.2
47.5°	116.5
50°	83.4
52.5°	59.0
55°	41.7
57.5°	31.6
60°	24.4
62.5°	20.1
65°	14.4
67.5°	11.5
70°	8.6
72.5°	7.2
75°	5.8
77.5°	2.9
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)