

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642248

Luminaire Tested: ML5612LSWFL5597FS1E - 694WB - 900LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-67)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSWFL5597FS1E - 694WB - 900LM - 3500K
Description: ML56 RR, 55D TIR OPTIC, 6" WHITE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1310.7 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642248

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694WB - 900LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642248

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694WB - 900LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92																			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85																			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78																			
4	95	87	81	76	93	86	80	76	84	79	75	81	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	63	61																			
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57																			
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	58	54	53																			
9	72	62	56	51	71	61	55	51	60	55	51	59	54	51	59	54	51	49																			
10	69	58	52	48	68	58	52	48	57	51	48	56	51	48	55	51	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74884
5°	71494
10°	67890
15°	64183
20°	58105
25°	49231
30°	39842
35°	30939
40°	22850
45°	15017
50°	7275
55°	3852
60°	2653
65°	2088
70°	1843
75°	1228
80°	726
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15017 cd/sqm



TEST NUMBER: P642248

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694WB - 900LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.6	9.3
10°-20°	314.7	24.0
20°-30°	371.8	28.4
30°-40°	289.9	22.1
40°-50°	148.2	11.3
50°-60°	40.5	3.1
60°-70°	16.6	1.3
70°-80°	6.7	0.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.1	61.7
0°-40°	1098.0	83.8
0°-60°	1286.7	98.2
0°-90°	1310.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1310.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1366	
5°	1299	122
15°	1131	315
25°	814	372
35°	462	290
45°	194	148
55°	40	40
65°	16	17
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P642248

CATALOG NUMBER: ML5612LSWFL5597FS1E - 694WB - 900LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1366.0
2.5°	1349.9
5°	1299.2
7.5°	1256.5
10°	1219.6
12.5°	1178.1
15°	1130.9
17.5°	1068.6
20°	996.0
22.5°	910.7
25°	813.9
27.5°	719.3
30°	629.4
32.5°	545.3
35°	462.3
37.5°	388.5
40°	319.3
42.5°	254.8
45°	193.7
47.5°	128.0
50°	85.3
52.5°	57.6
55°	40.3
57.5°	30.0
60°	24.2
62.5°	19.6
65°	16.1
67.5°	13.8
70°	11.5
72.5°	8.1
75°	5.8
77.5°	4.6
80°	2.3
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)