

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642394

Luminaire Tested: ML5615LSFL409FS1E - 592SC - 1500LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642394
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-25)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 592SC - 1500LM - 4000K
Description: ML56 RR, 40D TIR OPTIC, 5" SPECULAR CLEAR TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2016.9 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642394
CATALOG NUMBER: ML5615LSFL409FS1E - 592SC - 1500LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P642394

CATALOG NUMBER: ML5615LSFL409FS1E - 592SC - 1500LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94															
2	108	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88				88															
3	103	97	92	89	101	96	91	88	93	90	87	91	88	85	89	86	84	82				82															
4	98	91	86	82	97	90	85	81	88	84	80	86	82	80	84	81	79	77				77															
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	72				72															
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	70	68				68															
7	85	77	71	67	84	76	70	67	75	70	66	73	69	66	72	69	66	64				64															
8	82	72	67	63	80	72	67	63	71	66	63	70	65	62	69	65	62	61				61															
9	78	69	63	59	77	68	63	59	67	63	59	67	62	59	66	62	59	57				57															
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	55				55															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	269323
5°	260407
10°	227122
15°	187332
20°	144719
25°	108607
30°	78191
35°	53350
40°	33357
45°	18956
50°	6730
55°	3895
60°	2226
65°	654
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18956 cd/sqm



TEST NUMBER: P642394

CATALOG NUMBER: ML5615LSFL409FS1E - 592SC - 1500LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.8	14.8
10°-20°	631.6	31.3
20°-30°	572.8	28.4
30°-40°	349.9	17.3
40°-50°	132.3	6.6
50°-60°	26.8	1.3
60°-70°	4.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1503.2	74.5
0°-40°	1853.1	91.9
0°-60°	2012.2	99.8
0°-90°	2016.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2016.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3412	
5°	3286	299
15°	2292	632
25°	1247	573
35°	554	350
45°	170	132
55°	28	27
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642394

CATALOG NUMBER: ML5615LSFL409FS1E - 592SC - 1500LM - 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3411.7
2.5°	3385.2
5°	3286.2
7.5°	3089.8
10°	2833.4
12.5°	2566.3
15°	2292.2
17.5°	2003.9
20°	1722.7
22.5°	1469.7
25°	1246.9
27.5°	1043.5
30°	857.8
32.5°	693.3
35°	553.6
37.5°	431.6
40°	323.7
42.5°	244.1
45°	169.8
47.5°	95.5
50°	54.8
52.5°	38.9
55°	28.3
57.5°	19.5
60°	14.1
62.5°	8.8
65°	3.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)