

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642699

Luminaire Tested: ML5615LSFL409FS1E - 696WB - 900LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642699  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-46)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSFL409FS1E - 696WB - 900LM - 4000K  
Description: ML56 RR, 40D TIR OPTIC, 6" SHALLOW WHITE BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1311.9 lumens  
Efficiency: N/A  
Efficacy: 124.9 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642699  
CATALOG NUMBER: ML5615LSFL409FS1E - 696WB - 900LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642699

CATALOG NUMBER: ML5615LSFL409FS1E - 696WB - 900LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 100 | 98  | 97  | 96  | 95  | 94  |    |    |   |
| 2   | 108 | 103 | 99  | 96  | 106 | 101 | 98  | 95  | 98  | 95  | 93  | 95  | 93  | 91  | 93  | 91  | 89  | 87  |    |    |   |
| 3   | 103 | 96  | 91  | 87  | 101 | 95  | 90  | 87  | 92  | 89  | 85  | 90  | 87  | 84  | 88  | 85  | 83  | 81  |    |    |   |
| 4   | 98  | 90  | 85  | 81  | 96  | 89  | 84  | 80  | 87  | 83  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 76  |    |    |   |
| 5   | 93  | 85  | 79  | 75  | 91  | 84  | 78  | 74  | 82  | 77  | 74  | 80  | 76  | 73  | 79  | 75  | 72  | 71  |    |    |   |
| 6   | 88  | 80  | 74  | 70  | 87  | 79  | 73  | 69  | 77  | 72  | 69  | 76  | 72  | 68  | 75  | 71  | 68  | 66  |    |    |   |
| 7   | 84  | 75  | 69  | 65  | 83  | 74  | 69  | 65  | 73  | 68  | 65  | 72  | 68  | 64  | 71  | 67  | 64  | 63  |    |    |   |
| 8   | 80  | 71  | 65  | 61  | 79  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 63  | 60  | 59  |    |    |   |
| 9   | 77  | 67  | 62  | 58  | 76  | 67  | 61  | 58  | 66  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 56  |    |    |   |
| 10  | 73  | 64  | 58  | 55  | 72  | 64  | 58  | 55  | 63  | 58  | 54  | 62  | 57  | 54  | 61  | 57  | 54  | 53  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 116548 |
| 5°  | 112987 |
| 10° | 98612  |
| 15° | 80869  |
| 20° | 63040  |
| 25° | 47700  |
| 30° | 34379  |
| 35° | 23570  |
| 40° | 15450  |
| 45° | 10040  |
| 50° | 5910   |
| 55° | 3259   |
| 60° | 1864   |
| 65° | 1038   |
| 70° | 545    |
| 75° | 233    |
| 80° | 347    |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10040 cd/sqm



TEST NUMBER: P642699

CATALOG NUMBER: ML5615LSFL409FS1E - 696WB - 900LM - 4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 186.7  | 14.2      |
| 10°-20°   | 393.3  | 30.0      |
| 20°-30°   | 361.5  | 27.6      |
| 30°-40°   | 223.9  | 17.1      |
| 40°-50°   | 102.4  | 7.8       |
| 50°-60°   | 33.2   | 2.5       |
| 60°-70°   | 8.6    | 0.7       |
| 70°-80°   | 1.8    | 0.1       |
| 80°-90°   | 0.4    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 941.5  | 71.8      |
| 0°-40°    | 1165.4 | 88.8      |
| 0°-60°    | 1301.0 | 99.2      |
| 0°-90°    | 1311.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1311.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2126 |      |
| 5°  | 2053 | 187  |
| 15° | 1425 | 393  |
| 25° | 789  | 362  |
| 35° | 352  | 224  |
| 45° | 130  | 102  |
| 55° | 34   | 33   |
| 65° | 8    | 9    |
| 75° | 1    | 2    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P642699

CATALOG NUMBER: ML5615LSFL409FS1E - 696WB - 900LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2126.0 |
| 2.5°  | 2112.3 |
| 5°    | 2053.2 |
| 7.5°  | 1931.7 |
| 10°   | 1771.5 |
| 12.5° | 1591.9 |
| 15°   | 1424.9 |
| 17.5° | 1247.6 |
| 20°   | 1080.6 |
| 22.5° | 926.1  |
| 25°   | 788.6  |
| 27.5° | 660.2  |
| 30°   | 543.1  |
| 32.5° | 440.9  |
| 35°   | 352.2  |
| 37.5° | 278.4  |
| 40°   | 215.9  |
| 42.5° | 168.2  |
| 45°   | 129.5  |
| 47.5° | 96.6   |
| 50°   | 69.3   |
| 52.5° | 48.9   |
| 55°   | 34.1   |
| 57.5° | 23.9   |
| 60°   | 17.0   |
| 62.5° | 12.5   |
| 65°   | 8.0    |
| 67.5° | 4.5    |
| 70°   | 3.4    |
| 72.5° | 2.3    |
| 75°   | 1.1    |
| 77.5° | 1.1    |
| 80°   | 1.1    |
| 82.5° | 1.1    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)