

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642706

Luminaire Tested: ML5615LSNFL259FS1E - 591WB - 1500LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642706
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 591WB - 1500LM - 2700K
Description: ML56 RR, 25D TIR OPTIC, 5" DEADFRONT TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1651.3 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642706
CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1500LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642706

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1500LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75																			
5	92	84	78	74	90	83	77	73	81	76	73	79	75	72	78	74	71	70																			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66																			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62																			
8	80	71	65	61	79	70	64	61	69	64	60	68	63	60	67	63	60	58																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	58	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	327984
5°	299037
10°	218825
15°	124583
20°	76707
25°	62321
30°	51328
35°	41670
40°	33666
45°	26916
50°	17574
55°	7707
60°	4910
65°	4352
70°	3947
75°	3782
80°	4228
85°	4257

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26916 cd/sqm



TEST NUMBER: P642706

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1500LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	326.2	19.8
10°-20°	438.9	26.6
20°-30°	329.5	20.0
30°-40°	271.7	16.5
40°-50°	181.1	11.0
50°-60°	61.4	3.7
60°-70°	23.6	1.4
70°-80°	13.3	0.8
80°-90°	5.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1094.5	66.3
0°-40°	1366.2	82.7
0°-60°	1608.8	97.4
0°-90°	1651.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1651.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4155	
5°	3774	326
15°	1524	439
25°	716	330
35°	432	272
45°	241	181
55°	56	61
65°	23	24
75°	12	13
85°	5	6
90°	0	



TEST NUMBER: P642706

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1500LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	4154.8
2.5°	4069.2
5°	3773.7
7.5°	3299.2
10°	2729.9
12.5°	2095.3
15°	1524.4
17.5°	1130.9
20°	913.1
22.5°	799.5
25°	715.5
27.5°	634.6
30°	563.1
32.5°	494.7
35°	432.4
37.5°	376.4
40°	326.7
42.5°	281.5
45°	241.1
47.5°	188.2
50°	143.1
52.5°	98.0
55°	56.0
57.5°	37.3
60°	31.1
62.5°	28.0
65°	23.3
67.5°	20.2
70°	17.1
72.5°	14.0
75°	12.4
77.5°	10.9
80°	9.3
82.5°	7.8
85°	4.7
87.5°	3.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)