

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642435

Luminaire Tested: ML5615LSFL409FS1E - 593SNB - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642435
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-30)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 593SNB - 1200LM - 5000K
Description: ML56 RR, 40D TIR OPTIC, 5" SATIN NICKLE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1616.7 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642435
CATALOG NUMBER: ML5615LSFL409FS1E - 593SNB - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642435
 CATALOG NUMBER: ML5615LSFL409FS1E - 593SNB - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82																			
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77																			
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72																			
6	89	81	75	71	88	80	74	70	78	74	70	77	73	69	76	72	69	68																			
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64																			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60																			
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57																			
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	211609
5°	205119
10°	178674
15°	147024
20°	114527
25°	87180
30°	63315
35°	43241
40°	27123
45°	16054
50°	6005
55°	3565
60°	2037
65°	803
70°	323
75°	427
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16054 cd/sqm



TEST NUMBER: P642435

CATALOG NUMBER: ML5615LSFL409FS1E - 593SNB - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.1	14.5
10°-20°	496.5	30.7
20°-30°	459.0	28.4
30°-40°	284.1	17.6
40°-50°	110.8	6.9
50°-60°	24.7	1.5
60°-70°	5.6	0.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1190.5	73.6
0°-40°	1474.6	91.2
0°-60°	1610.1	99.6
0°-90°	1616.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1616.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2681	
5°	2588	235
15°	1799	496
25°	1001	459
35°	449	284
45°	144	111
55°	26	25
65°	4	6
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P642435

CATALOG NUMBER: ML5615LSFL409FS1E - 593SNB - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2680.6
2.5°	2664.8
5°	2588.5
7.5°	2428.9
10°	2229.0
12.5°	2014.7
15°	1799.0
17.5°	1573.3
20°	1363.3
22.5°	1172.0
25°	1000.9
27.5°	842.7
30°	694.6
32.5°	563.7
35°	448.7
37.5°	350.9
40°	263.2
42.5°	199.9
45°	143.8
47.5°	84.8
50°	48.9
52.5°	36.0
55°	25.9
57.5°	18.7
60°	12.9
62.5°	10.1
65°	4.3
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)