

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642800

Luminaire Tested: ML5615LSNFL259FS1E - 593TBZB - 1500LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 593TBZB - 1500LM - 5000K
Description: ML56 RR, 25D TIR OPTIC, 5" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1723.7 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642800

CATALOG NUMBER: ML5615LSNFL259FS1E - 593TBZB - 1500LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642800

CATALOG NUMBER: ML5615LSNFL259FS1E - 593TBZB - 1500LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100																
	1	114	111	109	107	111	109	107	105	105	104	102	101	100	99	98	97	96	94	94	94	94	94	94	94	94	94	94	94																
	2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89	89	89	89	89	89	89	89	89	89	89																
	3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83	83	83	83	83	83	83	83	83	83	83																
	4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78	78	78	78	78	78	78	78	78	78	78																
	5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74	74	74	74	74	74	74	74	74	74	74																
	6	91	82	77	73	89	82	77	73	80	76	72	79	75	72	78	74	71	70	70	70	70	70	70	70	70	70	70	70																
	7	87	78	73	69	86	78	72	69	76	72	68	75	71	68	74	71	68	66	66	66	66	66	66	66	66	66	66	66	66															
	8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63	63	63	63	63	63	63	63	63	63	63	63															
	9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60	60	60	60	60	60	60	60	60															
	10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58	58	58	58	58	58	58	58	58	58	58	58															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	376903
5°	346519
10°	253253
15°	145439
20°	87082
25°	70570
30°	57727
35°	46537
40°	35552
45°	19950
50°	5219
55°	2684
60°	1674
65°	654
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19950 cd/sqm



TEST NUMBER: P642800

CATALOG NUMBER: ML5615LSNFL259FS1E - 593TBZB - 1500LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	377.6	21.9
10°-20°	508.5	29.5
20°-30°	373.0	21.6
30°-40°	302.0	17.5
40°-50°	137.7	8.0
50°-60°	19.6	1.1
60°-70°	4.6	0.3
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1259.1	73.0
0°-40°	1561.1	90.6
0°-60°	1718.4	99.7
0°-90°	1723.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1723.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4774	
5°	4373	378
15°	1780	509
25°	810	373
35°	483	302
45°	179	138
55°	20	20
65°	4	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P642800

CATALOG NUMBER: ML5615LSNFL259FS1E - 593TBZB - 1500LM - 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4774.5
2.5°	4684.3
5°	4372.9
7.5°	3829.8
10°	3159.4
12.5°	2441.2
15°	1779.6
17.5°	1302.0
20°	1036.6
22.5°	905.7
25°	810.2
27.5°	718.2
30°	633.3
32.5°	555.5
35°	482.9
37.5°	417.5
40°	345.0
42.5°	256.5
45°	178.7
47.5°	99.1
50°	42.5
52.5°	26.5
55°	19.5
57.5°	15.9
60°	10.6
62.5°	7.1
65°	3.5
67.5°	1.8
70°	1.8
72.5°	1.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)