

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642450

Luminaire Tested: ML5615LSFL409FS1E - 593TBZB - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-31)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 593TBZB - 1200LM - 5000K
Description: ML56 RR, 40D TIR OPTIC, 5" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1598.0 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642450
CATALOG NUMBER: ML5615LSFL409FS1E - 593TBZB - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642450

CATALOG NUMBER: ML5615LSFL409FS1E - 593TBZB - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88																			
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82																			
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77																			
5	94	86	80	76	92	85	80	76	83	79	75	81	77	74	80	76	74	72																			
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68																			
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64																			
8	81	72	67	63	80	72	66	63	71	66	62	70	65	62	69	65	62	61																			
9	78	69	63	59	77	68	63	59	67	62	59	66	62	59	66	62	59	57																			
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	211585
5°	204866
10°	178289
15°	146501
20°	114216
25°	86962
30°	62814
35°	42846
40°	26535
45°	14937
50°	5477
55°	3165
60°	1816
65°	542
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14937 cd/sqm



TEST NUMBER: P642450

CATALOG NUMBER: ML5615LSFL409FS1E - 593TBZB - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.8	14.7
10°-20°	495.4	31.0
20°-30°	456.8	28.6
30°-40°	281.0	17.6
40°-50°	104.3	6.5
50°-60°	21.8	1.4
60°-70°	3.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1187.0	74.3
0°-40°	1468.0	91.9
0°-60°	1594.1	99.8
0°-90°	1598.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1598.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2680	
5°	2585	235
15°	1793	495
25°	998	457
35°	445	281
45°	134	104
55°	23	22
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642450

CATALOG NUMBER: ML5615LSFL409FS1E - 593TBZB - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2680.3
2.5°	2661.6
5°	2585.3
7.5°	2428.5
10°	2224.2
12.5°	2012.7
15°	1792.6
17.5°	1571.0
20°	1359.6
22.5°	1166.8
25°	998.4
27.5°	835.9
30°	689.1
32.5°	558.2
35°	444.6
37.5°	346.7
40°	257.5
42.5°	194.2
45°	133.8
47.5°	71.9
50°	44.6
52.5°	31.7
55°	23.0
57.5°	15.8
60°	11.5
62.5°	7.2
65°	2.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)