

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642823

Luminaire Tested: ML5615LSNFL259FS1E - 594SNB - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642823
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 594SNB - 1200LM - 3500K
Description: ML56 RR, 25D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1460.6 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642823

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642823

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78																			
4	96	88	82	78	94	87	81	77	84	80	76	82	78	75	81	77	74	73																			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																			
6	86	77	71	67	85	76	71	66	75	70	66	74	69	66	72	68	65	64																			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54																			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	283027
5°	257213
10°	187451
15°	106260
20°	65332
25°	52845
30°	43243
35°	34770
40°	27545
45°	21636
50°	16899
55°	13240
60°	10547
65°	8480
70°	6163
75°	3264
80°	1818
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21636 cd/sqm



TEST NUMBER: P642823

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	280.6	19.2
10°-20°	374.7	25.7
20°-30°	279.8	19.2
30°-40°	226.3	15.5
40°-50°	151.1	10.3
50°-60°	87.7	6.0
60°-70°	45.8	3.1
70°-80°	13.2	0.9
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.2	64.0
0°-40°	1161.5	79.5
0°-60°	1400.3	95.9
0°-90°	1460.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1460.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3585	
5°	3246	281
15°	1300	375
25°	607	280
35°	361	226
45°	194	151
55°	96	88
65°	45	46
75°	11	13
85°	0	1
90°	0	



TEST NUMBER: P642823

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3585.3
2.5°	3506.5
5°	3245.9
7.5°	2842.3
10°	2338.5
12.5°	1792.0
15°	1300.2
17.5°	963.5
20°	777.7
22.5°	681.5
25°	606.7
27.5°	538.5
30°	474.4
32.5°	414.3
35°	360.8
37.5°	311.4
40°	267.3
42.5°	228.5
45°	193.8
47.5°	163.0
50°	137.6
52.5°	114.9
55°	96.2
57.5°	80.2
60°	66.8
62.5°	56.1
65°	45.4
67.5°	37.4
70°	26.7
72.5°	17.4
75°	10.7
77.5°	6.7
80°	4.0
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)