

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642502

Luminaire Tested: ML5615LSFL409FS1E - 594TBZB - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-34)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 594TBZB - 900LM - 3000K
Description: ML56 RR, 40D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1176.7 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642502

CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P642502

CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81																			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	55	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150603
5°	145877
10°	126955
15°	104306
20°	81386
25°	61807
30°	44528
35°	30029
40°	19394
45°	12515
50°	7319
55°	4101
60°	2763
65°	1924
70°	1431
75°	1251
80°	455
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12515 cd/sqm



TEST NUMBER: P642502

CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.3	14.2
10°-20°	352.7	30.0
20°-30°	324.8	27.6
30°-40°	198.6	16.9
40°-50°	88.7	7.5
50°-60°	29.3	2.5
60°-70°	11.0	0.9
70°-80°	3.9	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	844.7	71.8
0°-40°	1043.3	88.7
0°-60°	1161.3	98.7
0°-90°	1176.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1176.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1908	
5°	1841	167
15°	1276	353
25°	710	325
35°	312	199
45°	112	89
55°	30	29
65°	10	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P642502

CATALOG NUMBER: ML5615LSFL409FS1E - 594TBZB - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1907.8
2.5°	1895.4
5°	1840.9
7.5°	1730.9
10°	1583.8
12.5°	1429.5
15°	1276.3
17.5°	1120.0
20°	968.8
22.5°	831.0
25°	709.6
27.5°	593.4
30°	488.5
32.5°	392.9
35°	311.6
37.5°	244.8
40°	188.2
42.5°	146.0
45°	112.1
47.5°	83.3
50°	59.6
52.5°	42.2
55°	29.8
57.5°	21.6
60°	17.5
62.5°	14.4
65°	10.3
67.5°	8.2
70°	6.2
72.5°	5.1
75°	4.1
77.5°	2.1
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)