

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642828

Luminaire Tested: ML5615LSNFL259FS1E - 594SNB - 1500LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642828
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 594SNB - 1500LM - 3500K
Description: ML56 RR, 25D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1795.7 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642828

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 1500LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642828

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 1500LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92				
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78				
4	96	88	82	78	94	87	81	77	84	80	76	82	78	75	81	77	74	73				
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68				
6	86	77	71	67	85	76	71	66	75	70	66	74	69	66	72	68	65	64				
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60				
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57				
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54				
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	347964
5°	316225
10°	230464
15°	130638
20°	80328
25°	64969
30°	53160
35°	42749
40°	33862
45°	26592
50°	20779
55°	16282
60°	12962
65°	10442
70°	7594
75°	3996
80°	2228
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26592 cd/sqm



TEST NUMBER: P642828

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 1500LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.0	19.2
10°-20°	460.7	25.7
20°-30°	344.0	19.2
30°-40°	278.3	15.5
40°-50°	185.8	10.3
50°-60°	107.8	6.0
60°-70°	56.4	3.1
70°-80°	16.2	0.9
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1149.7	64.0
0°-40°	1428.0	79.5
0°-60°	1721.6	95.9
0°-90°	1795.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1795.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4408	
5°	3991	345
15°	1598	461
25°	746	344
35°	444	278
45°	238	186
55°	118	108
65°	56	56
75°	13	16
85°	0	2
90°	0	



TEST NUMBER: P642828

CATALOG NUMBER: ML5615LSNFL259FS1E - 594SNB - 1500LM - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4407.9
2.5°	4310.9
5°	3990.6
7.5°	3494.4
10°	2875.1
12.5°	2203.1
15°	1598.5
17.5°	1184.5
20°	956.2
22.5°	837.9
25°	745.9
27.5°	662.1
30°	583.2
32.5°	509.3
35°	443.6
37.5°	382.8
40°	328.6
42.5°	280.9
45°	238.2
47.5°	200.4
50°	169.2
52.5°	141.3
55°	118.3
57.5°	98.6
60°	82.1
62.5°	69.0
65°	55.9
67.5°	46.0
70°	32.9
72.5°	21.4
75°	13.1
77.5°	8.2
80°	4.9
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)