

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642525

Luminaire Tested: ML5615LSFL409FS1E - 596WB - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 596WB - 1200LM - 5000K
Description: ML56 RR, 40D TIR OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1645.5 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.7
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642525
CATALOG NUMBER: ML5615LSFL409FS1E - 596WB - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642525

CATALOG NUMBER: ML5615LSFL409FS1E - 596WB - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71																			
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67																			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59																			
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	209517
5°	203011
10°	177095
15°	145856
20°	114023
25°	86753
30°	62978
35°	43279
40°	28328
45°	18320
50°	10427
55°	4363
60°	2952
65°	1606
70°	992
75°	885
80°	636
85°	1268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18320 cd/sqm



TEST NUMBER: P642525

CATALOG NUMBER: ML5615LSFL409FS1E - 596WB - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.9	14.2
10°-20°	492.8	30.0
20°-30°	456.2	27.7
30°-40°	285.0	17.3
40°-50°	128.7	7.8
50°-60°	35.9	2.2
60°-70°	9.9	0.6
70°-80°	3.0	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1181.9	71.8
0°-40°	1467.0	89.2
0°-60°	1631.5	99.2
0°-90°	1645.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1645.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2654	
5°	2562	233
15°	1785	493
25°	996	456
35°	449	285
45°	164	129
55°	32	36
65°	9	10
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P642525

CATALOG NUMBER: ML5615LSFL409FS1E - 596WB - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2654.1
2.5°	2638.2
5°	2561.9
7.5°	2407.9
10°	2209.3
12.5°	1996.3
15°	1784.7
17.5°	1564.5
20°	1357.3
22.5°	1167.3
25°	996.0
27.5°	833.3
30°	690.9
32.5°	561.3
35°	449.1
37.5°	354.1
40°	274.9
42.5°	213.0
45°	164.1
47.5°	118.0
50°	84.9
52.5°	56.1
55°	31.7
57.5°	23.0
60°	18.7
62.5°	14.4
65°	8.6
67.5°	5.8
70°	4.3
72.5°	2.9
75°	2.9
77.5°	2.9
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)