

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642527

Luminaire Tested: ML5615LSFL409FS1E - 596WB - 1500LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-35)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 596WB - 1500LM - 3000K
Description: ML56 RR, 40D TIR OPTIC, 5" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1829.6 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.7
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642527

CATALOG NUMBER: ML5615LSFL409FS1E - 596WB - 1500LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P642527

CATALOG NUMBER: ML5615LSFL409FS1E - 596WB - 1500LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71																			
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67																			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59																			
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	232963
5°	225738
10°	196918
15°	162185
20°	126784
25°	96465
30°	70024
35°	48117
40°	31502
45°	20363
50°	11593
55°	4845
60°	3284
65°	1793
70°	1108
75°	976
80°	727
85°	1449

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20363 cd/sqm



TEST NUMBER: P642527

CATALOG NUMBER: ML5615LSFL409FS1E - 596WB - 1500LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.9	14.2
10°-20°	548.0	30.0
20°-30°	507.3	27.7
30°-40°	316.9	17.3
40°-50°	143.1	7.8
50°-60°	39.9	2.2
60°-70°	11.0	0.6
70°-80°	3.4	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1314.2	71.8
0°-40°	1631.2	89.2
0°-60°	1814.2	99.2
0°-90°	1829.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1829.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2951	
5°	2849	259
15°	1984	548
25°	1108	507
35°	499	317
45°	182	143
55°	35	40
65°	10	11
75°	3	3
85°	2	1
90°	0	



TEST NUMBER: P642527

CATALOG NUMBER: ML5615LSFL409FS1E - 596WB - 1500LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2951.1
2.5°	2933.5
5°	2848.7
7.5°	2677.5
10°	2456.6
12.5°	2219.7
15°	1984.5
17.5°	1739.6
20°	1509.2
22.5°	1297.9
25°	1107.5
27.5°	926.6
30°	768.2
32.5°	624.2
35°	499.3
37.5°	393.7
40°	305.7
42.5°	236.9
45°	182.4
47.5°	131.2
50°	94.4
52.5°	62.4
55°	35.2
57.5°	25.6
60°	20.8
62.5°	16.0
65°	9.6
67.5°	6.4
70°	4.8
72.5°	3.2
75°	3.2
77.5°	3.2
80°	1.6
82.5°	1.6
85°	1.6
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)