

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642856

Luminaire Tested: ML5615LSNFL259FS1E - 594WB - 1500LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 594WB - 1500LM - 2700K
Description: ML56 RR, 25D TIR OPTIC, 5" WHITE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1712.0 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.44
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642856
CATALOG NUMBER: ML5615LSNFL259FS1E - 594WB - 1500LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642856

CATALOG NUMBER: ML5615LSNFL259FS1E - 594WB - 1500LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	98	97	97	95	94	92																			
2	107	102	97	94	105	100	96	93	97	93	90	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78																			
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73																			
5	91	82	76	72	89	81	75	71	79	74	71	78	73	70	76	72	69	68																			
6	86	77	71	67	85	76	71	66	75	70	66	73	69	65	72	68	65	63																			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56																			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54																			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	329894
5°	300709
10°	218168
15°	124558
20°	76951
25°	61903
30°	50471
35°	40620
40°	32378
45°	25521
50°	19858
55°	15621
60°	12520
65°	10161
70°	7178
75°	3782
80°	2819
85°	1449

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25521 cd/sqm



TEST NUMBER: P642856

CATALOG NUMBER: ML5615LSNFL259FS1E - 594WB - 1500LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.2	19.1
10°-20°	438.7	25.6
20°-30°	327.6	19.1
30°-40°	265.0	15.5
40°-50°	178.2	10.4
50°-60°	103.4	6.0
60°-70°	54.3	3.2
70°-80°	15.5	0.9
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1093.4	63.9
0°-40°	1358.4	79.3
0°-60°	1640.0	95.8
0°-90°	1712.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1712.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4179	
5°	3795	327
15°	1524	439
25°	711	328
35°	422	265
45°	229	178
55°	114	103
65°	54	54
75°	12	16
85°	2	2
90°	0	



TEST NUMBER: P642856

CATALOG NUMBER: ML5615LSNFL259FS1E - 594WB - 1500LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	4179.0
2.5°	4088.7
5°	3794.8
7.5°	3309.6
10°	2721.7
12.5°	2090.3
15°	1524.1
17.5°	1133.8
20°	916.0
22.5°	796.3
25°	710.7
27.5°	629.9
30°	553.7
32.5°	485.2
35°	421.5
37.5°	365.5
40°	314.2
42.5°	269.1
45°	228.6
47.5°	192.9
50°	161.7
52.5°	135.3
55°	113.5
57.5°	94.9
60°	79.3
62.5°	65.3
65°	54.4
67.5°	45.1
70°	31.1
72.5°	20.2
75°	12.4
77.5°	7.8
80°	6.2
82.5°	3.1
85°	1.6
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)