

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642553

Luminaire Tested: ML5615LSFL409FS1E - 692H - 1200LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642553  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-38)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSFL409FS1E - 692H - 1200LM - 3500K  
Description: ML56 RR, 40D TIR OPTIC, 6" HAZE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1526.1 lumens  
Efficiency: N/A  
Efficacy: 113.9 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642553  
CATALOG NUMBER: ML5615LSFL409FS1E - 692H - 1200LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P642553

CATALOG NUMBER: ML5615LSFL409FS1E - 692H - 1200LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	98	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82																			
4	98	91	85	81	96	90	85	81	87	83	80	86	82	79	84	81	78	77																			
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72																			
6	89	80	75	70	87	80	74	70	78	73	70	77	72	69	75	72	69	67																			
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63																			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60																			
9	77	68	62	59	76	68	62	58	67	62	58	66	61	58	65	61	58	57																			
10	74	65	59	55	73	64	59	55	64	59	55	63	58	55	62	58	55	54																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	138284
5°	133881
10°	116531
15°	95670
20°	74475
25°	56519
30°	40956
35°	28001
40°	18084
45°	11086
50°	5586
55°	2303
60°	1469
65°	519
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11086 cd/sqm



TEST NUMBER: P642553

CATALOG NUMBER: ML5615LSFL409FS1E - 692H - 1200LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	221.0	14.5
10°-20°	465.5	30.5
20°-30°	428.6	28.1
30°-40°	265.5	17.4
40°-50°	114.8	7.5
50°-60°	25.9	1.7
60°-70°	4.9	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1115.1	73.1
0°-40°	1380.5	90.5
0°-60°	1521.2	99.7
0°-90°	1526.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1526.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2522	
5°	2433	221
15°	1686	466
25°	934	429
35°	418	265
45°	143	115
55°	24	26
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642553

CATALOG NUMBER: ML5615LSFL409FS1E - 692H - 1200LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2522.5
2.5°	2505.1
5°	2432.9
7.5°	2284.5
10°	2093.4
12.5°	1891.5
15°	1685.7
17.5°	1474.5
20°	1276.6
22.5°	1096.2
25°	934.4
27.5°	784.7
30°	647.0
32.5°	525.4
35°	418.4
37.5°	327.5
40°	252.7
42.5°	195.2
45°	143.0
47.5°	105.6
50°	65.5
52.5°	34.8
55°	24.1
57.5°	18.7
60°	13.4
62.5°	8.0
65°	4.0
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)