

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642582

Luminaire Tested: ML5615LSFL409FS1E - 692W - 1200LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642582  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-39)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSFL409FS1E - 692W - 1200LM - 3000K  
Description: ML56 RR, 40D TIR OPTIC, 6" WHITE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1489.5 lumens  
Efficiency: N/A  
Efficacy: 111.2 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642582  
CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 1200LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642582

CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 1200LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	98	96	95	94			94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			87
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81			81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	78	76			76
5	93	85	79	75	91	84	79	75	82	78	74	80	76	73	79	75	73	71			71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59			59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56			56
10	74	64	59	55	73	64	58	55	63	58	55	62	58	55	62	57	54	53			53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	133060
5°	128989
10°	112389
15°	92305
20°	72054
25°	54808
30°	39747
35°	27231
40°	17676
45°	10986
50°	5765
55°	2609
60°	1710
65°	1012
70°	625
75°	551
80°	821
85°	818

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10986 cd/sqm



TEST NUMBER: P642582

CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 1200LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	213.0	14.3
10°-20°	449.2	30.2
20°-30°	415.4	27.9
30°-40°	258.2	17.3
40°-50°	113.4	7.6
50°-60°	27.9	1.9
60°-70°	8.1	0.5
70°-80°	3.3	0.2
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1077.5	72.3
0°-40°	1335.7	89.7
0°-60°	1477.0	99.2
0°-90°	1489.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1489.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2427	
5°	2344	213
15°	1626	449
25°	906	415
35°	407	258
45°	142	113
55°	27	28
65°	8	8
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P642582  
CATALOG NUMBER: ML5615LSFL409FS1E - 692W - 1200LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2427.2
2.5°	2411.6
5°	2344.0
7.5°	2202.3
10°	2019.0
12.5°	1824.0
15°	1626.4
17.5°	1422.3
20°	1235.1
22.5°	1060.8
25°	906.1
27.5°	761.8
30°	627.9
32.5°	509.6
35°	406.9
37.5°	319.8
40°	247.0
42.5°	191.1
45°	141.7
47.5°	105.3
50°	67.6
52.5°	36.4
55°	27.3
57.5°	20.8
60°	15.6
62.5°	11.7
65°	7.8
67.5°	3.9
70°	3.9
72.5°	3.9
75°	2.6
77.5°	2.6
80°	2.6
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)