

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642907

Luminaire Tested: ML5615LSNFL259FS1E - 692H - 900LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642907  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 692H - 900LM - 3000K  
Description: ML56 RR, 25D TIR OPTIC, 6" HAZE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1091.3 lumens  
Efficiency: N/A  
Efficacy: 103.9 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642907  
CATALOG NUMBER: ML5615LSNFL259FS1E - 692H - 900LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642907

CATALOG NUMBER: ML5615LSNFL259FS1E - 692H - 900LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94																
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88																
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82			82																
4	98	91	86	82	96	90	85	81	88	84	80	86	82	79	84	81	78	77			77																
5	94	86	80	76	92	85	79	76	83	78	75	81	77	74	80	76	74	72			72																
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68			68																
7	85	77	71	67	84	76	70	67	75	70	66	73	69	66	72	69	66	64			64																
8	82	73	67	63	81	72	67	63	71	66	63	70	66	62	69	65	62	61			61																
9	78	69	64	60	77	69	63	60	68	63	60	67	63	59	66	62	59	58			58																
10	75	66	61	57	74	66	60	57	65	60	57	64	60	57	63	59	56	55			55																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	156117
5°	142389
10°	104635
15°	60494
20°	37570
25°	30183
30°	24681
35°	19970
40°	15758
45°	11885
50°	6141
55°	1768
60°	1129
65°	662
70°	337
75°	212
80°	316
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11885 cd/sqm



TEST NUMBER: P642907

CATALOG NUMBER: ML5615LSNFL259FS1E - 692H - 900LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	224.0	20.5
10°-20°	305.9	28.0
20°-30°	230.3	21.1
30°-40°	187.0	17.1
40°-50°	114.1	10.5
50°-60°	23.5	2.2
60°-70°	5.1	0.5
70°-80°	1.2	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	760.2	69.7
0°-40°	947.2	86.8
0°-60°	1084.9	99.4
0°-90°	1091.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1091.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2848	
5°	2588	224
15°	1066	306
25°	499	230
35°	298	187
45°	153	114
55°	18	24
65°	5	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P642907

CATALOG NUMBER: ML5615LSNFL259FS1E - 692H - 900LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2847.8
2.5°	2787.1
5°	2587.5
7.5°	2268.6
10°	1879.7
12.5°	1447.6
15°	1065.9
17.5°	798.4
20°	644.0
22.5°	560.7
25°	499.0
27.5°	442.4
30°	389.9
32.5°	343.6
35°	298.4
37.5°	257.2
40°	220.2
42.5°	187.2
45°	153.3
47.5°	111.1
50°	72.0
52.5°	34.0
55°	18.5
57.5°	13.4
60°	10.3
62.5°	7.2
65°	5.1
67.5°	2.1
70°	2.1
72.5°	1.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)