

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642924

Luminaire Tested: ML5615LSNFL259FS1E - 692SC - 900LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642924  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 692SC - 900LM - 4000K  
Description: ML56 RR, 25D TIR OPTIC, 6" SPECULAR CLEAR TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1226.6 lumens  
Efficiency: N/A  
Efficacy: 116.8 lumens/watt  
Spacing Criteria (0/90/45): 0.37 / 0.37 / 0.39  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642924  
CATALOG NUMBER: ML5615LSNFL259FS1E - 692SC - 900LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642924

CATALOG NUMBER: ML5615LSNFL259FS1E - 692SC - 900LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89																			
3	104	98	93	89	102	96	92	89	94	90	87	91	89	86	89	87	85	83																			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78																			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74																			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70																			
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66																			
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63																			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	220843
5°	191580
10°	124664
15°	67645
20°	40609
25°	32197
30°	26207
35°	21007
40°	16524
45°	12606
50°	6499
55°	1520
60°	877
65°	441
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12606 cd/sqm



TEST NUMBER: P642924

CATALOG NUMBER: ML5615LSNFL259FS1E - 692SC - 900LM - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	290.9	23.7
10°-20°	346.1	28.2
20°-30°	246.2	20.1
30°-40°	197.2	16.1
40°-50°	120.3	9.8
50°-60°	22.4	1.8
60°-70°	3.5	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	883.2	72.0
0°-40°	1080.4	88.1
0°-60°	1223.2	99.7
0°-90°	1226.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1226.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4028	
5°	3481	291
15°	1192	346
25°	532	246
35°	314	197
45°	163	120
55°	16	22
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642924

CATALOG NUMBER: ML5615LSNFL259FS1E - 692SC - 900LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4028.5
2.5°	3908.0
5°	3481.4
7.5°	2858.2
10°	2239.5
12.5°	1666.2
15°	1191.9
17.5°	875.8
20°	696.1
22.5°	601.7
25°	532.3
27.5°	470.9
30°	414.0
32.5°	362.8
35°	313.9
37.5°	270.7
40°	230.9
42.5°	196.8
45°	162.6
47.5°	117.1
50°	76.2
52.5°	34.1
55°	15.9
57.5°	10.2
60°	8.0
62.5°	5.7
65°	3.4
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)