

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642936

Luminaire Tested: ML5615LSNFL259FS1E - 692W - 900LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642936  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 692W - 900LM - 2700K  
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1070.0 lumens  
Efficiency: N/A  
Efficacy: 101.9 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642936

CATALOG NUMBER: ML5615LSNFL259FS1E - 692W - 900LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P642936

CATALOG NUMBER: ML5615LSNFL259FS1E - 692W - 900LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66			
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	62			
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	61	57	56			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	54			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	148475
5°	135505
10°	99397
15°	56970
20°	35114
25°	28544
30°	23605
35°	19267
40°	15450
45°	12017
50°	6652
55°	2581
60°	2083
65°	1816
70°	1603
75°	1694
80°	1578
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12017 cd/sqm



TEST NUMBER: P642936

CATALOG NUMBER: ML5615LSNFL259FS1E - 692W - 900LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	213.0	19.9
10°-20°	288.7	27.0
20°-30°	217.6	20.3
30°-40°	180.4	16.9
40°-50°	115.1	10.8
50°-60°	30.6	2.9
60°-70°	14.2	1.3
70°-80°	8.0	0.8
80°-90°	2.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	719.3	67.2
0°-40°	899.7	84.1
0°-60°	1045.4	97.7
0°-90°	1070.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1070.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2708	
5°	2462	213
15°	1004	289
25°	472	218
35°	288	180
45°	155	115
55°	27	31
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P642936

CATALOG NUMBER: ML5615LSNFL259FS1E - 692W - 900LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2708.4
2.5°	2652.4
5°	2462.4
7.5°	2156.5
10°	1785.6
12.5°	1373.7
15°	1003.8
17.5°	748.8
20°	601.9
22.5°	527.9
25°	471.9
27.5°	419.9
30°	372.9
32.5°	328.9
35°	287.9
37.5°	249.9
40°	215.9
42.5°	185.0
45°	155.0
47.5°	115.0
50°	78.0
52.5°	41.0
55°	27.0
57.5°	22.0
60°	19.0
62.5°	17.0
65°	14.0
67.5°	12.0
70°	10.0
72.5°	9.0
75°	8.0
77.5°	6.0
80°	5.0
82.5°	3.0
85°	2.0
87.5°	1.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)