

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642626

Luminaire Tested: ML5615LSFL409FS1E - 693TBZB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642626
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-43)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 693TBZB - 1200LM - 2700K
Description: ML56 RR, 40D TIR OPTIC, 6" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1429.2 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642626
CATALOG NUMBER: ML5615LSFL409FS1E - 693TBZB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642626
 CATALOG NUMBER: ML5615LSFL409FS1E - 693TBZB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	98	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82																			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77																			
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72																			
6	89	80	75	70	87	80	74	70	78	73	70	77	72	69	75	72	69	67																			
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63																			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60																			
9	77	68	62	59	76	68	62	58	67	62	58	66	61	58	65	61	58	57																			
10	74	65	59	55	73	64	59	55	63	59	55	63	58	55	62	58	55	54																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128888
5°	124851
10°	108754
15°	89410
20°	69685
25°	52963
30°	38525
35°	26254
40°	16932
45°	10497
50°	5288
55°	2179
60°	1250
65°	493
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10497 cd/sqm



TEST NUMBER: P642626

CATALOG NUMBER: ML5615LSFL409FS1E - 693TBZB - 1200LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.3	14.4
10°-20°	435.2	30.4
20°-30°	401.9	28.1
30°-40°	249.4	17.5
40°-50°	107.9	7.6
50°-60°	24.0	1.7
60°-70°	4.5	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1043.3	73.0
0°-40°	1292.7	90.5
0°-60°	1424.7	99.7
0°-90°	1429.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1429.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2351	
5°	2269	206
15°	1575	435
25°	876	402
35°	392	249
45°	135	108
55°	23	24
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P642626

CATALOG NUMBER: ML5615LSFL409FS1E - 693TBZB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2351.1
2.5°	2337.2
5°	2268.8
7.5°	2134.7
10°	1953.7
12.5°	1767.7
15°	1575.4
17.5°	1379.3
20°	1194.5
22.5°	1026.2
25°	875.6
27.5°	737.7
30°	608.6
32.5°	493.5
35°	392.3
37.5°	308.8
40°	236.6
42.5°	183.5
45°	135.4
47.5°	98.7
50°	62.0
52.5°	32.9
55°	22.8
57.5°	16.4
60°	11.4
62.5°	7.6
65°	3.8
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)