

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642643

Luminaire Tested: ML5615LSFL409FS1E - 693WB - 1200LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642643  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-40)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSFL409FS1E - 693WB - 1200LM - 3500K  
Description: ML56 RR, 40D TIR OPTIC, 6" WHITE BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1528.7 lumens  
Efficiency: N/A  
Efficacy: 114.1 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642643

CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1200LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P642643

CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1200LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	78	76																			
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63																			
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56																			
10	74	64	59	55	73	64	58	55	63	58	55	62	58	55	62	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	136349
5°	132165
10°	115095
15°	94666
20°	73839
25°	56265
30°	40778
35°	27994
40°	18170
45°	11296
50°	6038
55°	2552
60°	1754
65°	1038
70°	641
75°	572
80°	852
85°	818

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11296 cd/sqm



TEST NUMBER: P642643

CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1200LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	218.3	14.3
10°-20°	460.7	30.1
20°-30°	426.0	27.9
30°-40°	265.4	17.4
40°-50°	116.7	7.6
50°-60°	28.5	1.9
60°-70°	8.4	0.5
70°-80°	3.4	0.2
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1104.9	72.3
0°-40°	1370.3	89.6
0°-60°	1515.5	99.1
0°-90°	1528.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1528.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2487	
5°	2402	218
15°	1668	461
25°	930	426
35°	418	265
45°	146	117
55°	27	29
65°	8	8
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P642643

CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1200LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2487.2
2.5°	2471.2
5°	2401.7
7.5°	2258.7
10°	2067.6
12.5°	1868.4
15°	1668.0
17.5°	1462.1
20°	1265.7
22.5°	1087.9
25°	930.2
27.5°	780.5
30°	644.2
32.5°	523.9
35°	418.3
37.5°	328.8
40°	253.9
42.5°	196.5
45°	145.7
47.5°	108.3
50°	70.8
52.5°	37.4
55°	26.7
57.5°	21.4
60°	16.0
62.5°	12.0
65°	8.0
67.5°	4.0
70°	4.0
72.5°	4.0
75°	2.7
77.5°	2.7
80°	2.7
82.5°	1.3
85°	1.3
87.5°	1.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)