

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642975

Luminaire Tested: ML5615LSNFL259FS1E - 693TBZB - 1200LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642975  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 693TBZB - 1200LM - 5000K  
Description: ML56 RR, 25D TIR OPTIC, 6" TUSCON BRONZE BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1454.1 lumens  
Efficiency: N/A  
Efficacy: 108.5 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642975

CATALOG NUMBER: ML5615LSNFL259FS1E - 693TBZB - 1200LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642975

CATALOG NUMBER: ML5615LSNFL259FS1E - 693TBZB - 1200LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88				
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82				
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77				
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	72				
6	90	81	75	71	88	80	75	71	79	74	71	77	73	70	76	73	70	68				
7	86	77	71	67	84	76	71	67	75	70	67	74	69	66	73	69	66	65				
8	82	73	67	63	81	72	67	63	71	66	63	70	66	63	69	65	63	61				
9	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	62	59	58				
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	211929
5°	193341
10°	141119
15°	80755
20°	49267
25°	39946
30°	32878
35°	26669
40°	21104
45°	16172
50°	8221
55°	2064
60°	1261
65°	558
70°	224
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16172 cd/sqm



TEST NUMBER: P642975

CATALOG NUMBER: ML5615LSNFL259FS1E - 693TBZB - 1200LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	303.6	20.9
10°-20°	408.1	28.1
20°-30°	304.2	20.9
30°-40°	249.9	17.2
40°-50°	153.9	10.6
50°-60°	29.2	2.0
60°-70°	4.7	0.3
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1015.9	69.9
0°-40°	1265.8	87.0
0°-60°	1448.9	99.6
0°-90°	1454.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1454.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3866	
5°	3513	304
15°	1423	408
25°	660	304
35°	398	250
45°	209	154
55°	22	29
65°	4	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P642975

CATALOG NUMBER: ML5615LSNFL259FS1E - 693TBZB - 1200LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3865.9
2.5°	3788.2
5°	3513.4
7.5°	3073.2
10°	2535.1
12.5°	1949.5
15°	1422.9
17.5°	1050.3
20°	844.5
22.5°	738.1
25°	660.4
27.5°	585.6
30°	519.4
32.5°	457.5
35°	398.5
37.5°	345.3
40°	294.9
42.5°	251.8
45°	208.6
47.5°	149.6
50°	96.4
52.5°	43.2
55°	21.6
57.5°	14.4
60°	11.5
62.5°	7.2
65°	4.3
67.5°	1.4
70°	1.4
72.5°	1.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)