

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642976

Luminaire Tested: ML5615LSNFL259FS1E - 693TBZB - 1500LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 693TBZB - 1500LM - 2700K
Description: ML56 RR, 25D TIR OPTIC, 6" TUSCON BRONZE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1572.1 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642976

CATALOG NUMBER: ML5615LSNFL259FS1E - 693TBZB - 1500LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P642976

CATALOG NUMBER: ML5615LSNFL259FS1E - 693TBZB - 1500LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88																			
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	88	86	84	82																			
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77																			
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	72																			
6	90	81	75	71	88	80	75	71	79	74	71	77	73	70	76	73	70	68																			
7	86	77	71	67	84	76	71	67	75	70	67	74	69	66	73	69	66	65																			
8	82	73	67	63	81	72	67	63	71	66	63	70	66	63	69	65	63	61																			
9	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	62	59	58																			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	229104
5°	209013
10°	152552
15°	87299
20°	53263
25°	43182
30°	35543
35°	28830
40°	22814
45°	17482
50°	8887
55°	2227
60°	1360
65°	610
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17482 cd/sqm



TEST NUMBER: P642976

CATALOG NUMBER: ML5615LSNFL259FS1E - 693TBZB - 1500LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.2	20.9
10°-20°	441.2	28.1
20°-30°	328.9	20.9
30°-40°	270.1	17.2
40°-50°	166.3	10.6
50°-60°	31.6	2.0
60°-70°	5.2	0.3
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1098.2	69.9
0°-40°	1368.3	87.0
0°-60°	1566.3	99.6
0°-90°	1572.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1572.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4179	
5°	3798	328
15°	1538	441
25°	714	329
35°	431	270
45°	226	166
55°	23	32
65°	5	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P642976

CATALOG NUMBER: ML5615LSNFL259FS1E - 693TBZB - 1500LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	4179.2
2.5°	4095.2
5°	3798.2
7.5°	3322.2
10°	2740.5
12.5°	2107.5
15°	1538.2
17.5°	1135.4
20°	913.0
22.5°	797.9
25°	713.9
27.5°	633.0
30°	561.5
32.5°	494.6
35°	430.8
37.5°	373.3
40°	318.8
42.5°	272.2
45°	225.5
47.5°	161.8
50°	104.2
52.5°	46.7
55°	23.3
57.5°	15.6
60°	12.4
62.5°	7.8
65°	4.7
67.5°	1.6
70°	1.6
72.5°	1.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)