

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642645

Luminaire Tested: ML5615LSFL409FS1E - 693WB - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-40)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSFL409FS1E - 693WB - 1200LM - 5000K
Description: ML56 RR, 40D TIR OPTIC, 6" WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1645.4 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642645
CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P642645

CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	78	76																			
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63																			
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56																			
10	74	64	59	55	73	64	58	55	63	58	55	62	58	55	62	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146765
5°	142257
10°	123884
15°	101890
20°	79474
25°	60560
30°	43893
35°	30135
40°	19558
45°	12156
50°	6499
55°	2753
60°	1897
65°	1116
70°	689
75°	614
80°	916
85°	881

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12156 cd/sqm



TEST NUMBER: P642645

CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.9	14.3
10°-20°	495.9	30.1
20°-30°	458.5	27.9
30°-40°	285.6	17.4
40°-50°	125.6	7.6
50°-60°	30.7	1.9
60°-70°	9.0	0.5
70°-80°	3.6	0.2
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1189.3	72.3
0°-40°	1474.9	89.6
0°-60°	1631.3	99.1
0°-90°	1645.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1645.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2677	
5°	2585	235
15°	1795	496
25°	1001	458
35°	450	286
45°	157	126
55°	29	31
65°	9	9
75°	3	4
85°	1	2
90°	0	



TEST NUMBER: P642645

CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2677.2
2.5°	2659.9
5°	2585.1
7.5°	2431.2
10°	2225.5
12.5°	2011.1
15°	1795.3
17.5°	1573.8
20°	1362.3
22.5°	1171.0
25°	1001.2
27.5°	840.1
30°	693.4
32.5°	563.9
35°	450.3
37.5°	353.9
40°	273.3
42.5°	211.5
45°	156.8
47.5°	116.5
50°	76.2
52.5°	40.3
55°	28.8
57.5°	23.0
60°	17.3
62.5°	12.9
65°	8.6
67.5°	4.3
70°	4.3
72.5°	4.3
75°	2.9
77.5°	2.9
80°	2.9
82.5°	1.4
85°	1.4
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)