

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642993

Luminaire Tested: ML5615LSNFL259FS1E - 693WB - 1500LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642993
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 693WB - 1500LM - 3500K
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1753.0 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 17.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642993
CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 1500LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P642993

CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 1500LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	71	65	61	70	64	61	68	64	61	68	63	60	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56																			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	242925
5°	221698
10°	162984
15°	92878
20°	57224
25°	46708
30°	38481
35°	31561
40°	25283
45°	19870
50°	11351
55°	4081
60°	3421
65°	2983
70°	2629
75°	2775
80°	3125
85°	3082

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19870 cd/sqm



TEST NUMBER: P642993

CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 1500LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.7	19.9
10°-20°	471.9	26.9
20°-30°	355.5	20.3
30°-40°	295.0	16.8
40°-50°	190.1	10.8
50°-60°	50.4	2.9
60°-70°	22.5	1.3
70°-80°	13.9	0.8
80°-90°	4.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1176.0	67.1
0°-40°	1471.1	83.9
0°-60°	1711.6	97.6
0°-90°	1753.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1753.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4431	
5°	4029	349
15°	1636	472
25°	772	355
35°	472	295
45°	256	190
55°	43	50
65°	23	23
75°	13	14
85°	5	5
90°	0	



TEST NUMBER: P642993

CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 1500LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	4431.3
2.5°	4344.2
5°	4028.7
7.5°	3527.6
10°	2927.9
12.5°	2249.3
15°	1636.5
17.5°	1224.1
20°	980.9
22.5°	861.0
25°	772.2
27.5°	686.8
30°	607.9
32.5°	537.3
35°	471.6
37.5°	409.1
40°	353.3
42.5°	304.0
45°	256.3
47.5°	190.6
50°	133.1
52.5°	69.0
55°	42.7
57.5°	34.5
60°	31.2
62.5°	26.3
65°	23.0
67.5°	18.1
70°	16.4
72.5°	14.8
75°	13.1
77.5°	11.5
80°	9.9
82.5°	6.6
85°	4.9
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)