

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642650

Luminaire Tested: ML5615LSFL409FS1E - 693WB - 1500LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642650  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-40)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSFL409FS1E - 693WB - 1500LM - 5000K  
Description: ML56 RR, 40D TIR OPTIC, 6" WHITE BAFFLE TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2023.0 lumens  
Efficiency: N/A  
Efficacy: 118.3 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 17.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642650  
CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1500LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P642650

CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1500LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	78	76																			
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63																			
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56																			
10	74	64	59	55	73	64	58	55	63	58	55	62	58	55	62	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	180435
5°	174895
10°	152302
15°	125267
20°	97711
25°	74460
30°	53964
35°	37049
40°	24045
45°	14947
50°	7991
55°	3383
60°	2324
65°	1375
70°	850
75°	741
80°	1105
85°	1132

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14947 cd/sqm



TEST NUMBER: P642650

CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1500LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	288.8	14.3
10°-20°	609.7	30.1
20°-30°	563.7	27.9
30°-40°	351.2	17.4
40°-50°	154.5	7.6
50°-60°	37.8	1.9
60°-70°	11.1	0.5
70°-80°	4.4	0.2
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1462.2	72.3
0°-40°	1813.3	89.6
0°-60°	2005.6	99.1
0°-90°	2023.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2023.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3291	
5°	3178	289
15°	2207	610
25°	1231	564
35°	554	351
45°	193	154
55°	35	38
65°	11	11
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P642650

CATALOG NUMBER: ML5615LSFL409FS1E - 693WB - 1500LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3291.4
2.5°	3270.2
5°	3178.2
7.5°	2989.0
10°	2736.0
12.5°	2472.5
15°	2207.2
17.5°	1934.9
20°	1674.9
22.5°	1439.7
25°	1231.0
27.5°	1032.9
30°	852.5
32.5°	693.3
35°	553.6
37.5°	435.1
40°	336.0
42.5°	260.0
45°	192.8
47.5°	143.3
50°	93.7
52.5°	49.5
55°	35.4
57.5°	28.3
60°	21.2
62.5°	15.9
65°	10.6
67.5°	5.3
70°	5.3
72.5°	5.3
75°	3.5
77.5°	3.5
80°	3.5
82.5°	1.8
85°	1.8
87.5°	1.8
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)