

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642997

Luminaire Tested: ML5615LSNFL259FS1E - 693WB - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P642997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 693WB - 900LM - 3000K
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE BAFFLE TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1097.5 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P642997

CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P642997

CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	71	65	61	70	64	61	68	64	61	68	63	60	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56																			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152088
5°	138801
10°	102041
15°	58150
20°	35826
25°	29246
30°	24092
35°	19756
40°	15830
45°	12443
50°	7104
55°	2552
60°	2138
65°	1868
70°	1651
75°	1737
80°	1957
85°	1950

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12443 cd/sqm



TEST NUMBER: P642997

CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.3	19.9
10°-20°	295.5	26.9
20°-30°	222.5	20.3
30°-40°	184.7	16.8
40°-50°	119.0	10.8
50°-60°	31.6	2.9
60°-70°	14.1	1.3
70°-80°	8.7	0.8
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	736.3	67.1
0°-40°	921.0	83.9
0°-60°	1071.6	97.6
0°-90°	1097.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1097.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2774	
5°	2522	218
15°	1025	295
25°	484	223
35°	295	185
45°	160	119
55°	27	32
65°	14	14
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P642997

CATALOG NUMBER: ML5615LSNFL259FS1E - 693WB - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2774.3
2.5°	2719.8
5°	2522.3
7.5°	2208.6
10°	1833.1
12.5°	1408.3
15°	1024.6
17.5°	766.4
20°	614.1
22.5°	539.0
25°	483.5
27.5°	430.0
30°	380.6
32.5°	336.4
35°	295.2
37.5°	256.1
40°	221.2
42.5°	190.3
45°	160.5
47.5°	119.3
50°	83.3
52.5°	43.2
55°	26.7
57.5°	21.6
60°	19.5
62.5°	16.5
65°	14.4
67.5°	11.3
70°	10.3
72.5°	9.3
75°	8.2
77.5°	7.2
80°	6.2
82.5°	4.1
85°	3.1
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)