

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P643003

Luminaire Tested: ML5615LSNFL259FS1E - 694TBZB - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P643003
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-22)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5615LSNFL259FS1E - 694TBZB - 1200LM - 3500K
Description: ML56 RR, 25D TIR OPTIC, 6" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1460.6 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.43
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P643003

CATALOG NUMBER: ML5615LSNFL259FS1E - 694TBZB - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P643003

CATALOG NUMBER: ML5615LSNFL259FS1E - 694TBZB - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79																			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73																			
5	91	82	76	72	89	81	76	71	80	75	71	78	74	70	76	73	70	68																			
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64																			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60																			
8	79	69	63	59	78	69	63	59	68	62	59	67	62	58	66	61	58	57																			
9	75	66	60	56	74	65	60	56	64	59	56	63	59	55	63	58	55	54																			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	197183
5°	180205
10°	131622
15°	74643
20°	45539
25°	36546
30°	29783
35°	23885
40°	18943
45°	14815
50°	11513
55°	9070
60°	7181
65°	5889
70°	4280
75°	2542
80°	1263
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14815 cd/sqm



TEST NUMBER: P643003

CATALOG NUMBER: ML5615LSNFL259FS1E - 694TBZB - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.9	19.4
10°-20°	378.8	25.9
20°-30°	278.8	19.1
30°-40°	224.4	15.4
40°-50°	149.1	10.2
50°-60°	86.3	5.9
60°-70°	45.4	3.1
70°-80°	13.5	0.9
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	940.5	64.4
0°-40°	1165.0	79.8
0°-60°	1400.4	95.9
0°-90°	1460.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1460.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3597	
5°	3275	283
15°	1315	379
25°	604	279
35°	357	224
45°	191	149
55°	95	86
65°	45	45
75°	12	14
85°	0	1
90°	0	



TEST NUMBER: P643003

CATALOG NUMBER: ML5615LSNFL259FS1E - 694TBZB - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3596.9
2.5°	3524.7
5°	3274.7
7.5°	2864.4
10°	2364.5
12.5°	1817.8
15°	1315.2
17.5°	971.7
20°	780.6
22.5°	679.0
25°	604.2
27.5°	536.0
30°	470.5
32.5°	411.7
35°	356.9
37.5°	308.8
40°	264.7
42.5°	224.6
45°	191.1
47.5°	161.7
50°	135.0
52.5°	113.6
55°	94.9
57.5°	78.9
60°	65.5
62.5°	54.8
65°	45.4
67.5°	37.4
70°	26.7
72.5°	17.4
75°	12.0
77.5°	6.7
80°	4.0
82.5°	2.7
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)