

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P642701

Luminaire Tested: ML5615LSNFL259FS1E - 591WB - 1200LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P642701  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5615LSNFL259FS1E - 591WB - 1200LM - 2700K  
Description: ML56 RR, 25D TIR OPTIC, 5" DEADFRONT TRIM  
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1343.1 lumens  
Efficiency: N/A  
Efficacy: 100.2 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P642701  
CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1200LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P642701

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1200LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75																			
5	92	84	78	74	90	83	77	73	81	76	73	79	75	72	78	74	71	70																			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66																			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62																			
8	80	71	65	61	79	70	64	61	69	64	60	68	63	60	67	63	60	58																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	58	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	266773
5°	243227
10°	177992
15°	101332
20°	62392
25°	50693
30°	41748
35°	33893
40°	27380
45°	21892
50°	14295
55°	6262
60°	3994
65°	3549
70°	3208
75°	3081
80°	3455
85°	3442

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21892 cd/sqm



TEST NUMBER: P642701

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1200LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	265.3	19.8
10°-20°	357.0	26.6
20°-30°	268.0	20.0
30°-40°	221.0	16.5
40°-50°	147.3	11.0
50°-60°	50.0	3.7
60°-70°	19.2	1.4
70°-80°	10.9	0.8
80°-90°	4.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	890.3	66.3
0°-40°	1111.3	82.7
0°-60°	1308.6	97.4
0°-90°	1343.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1343.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3379	
5°	3069	265
15°	1240	357
25°	582	268
35°	352	221
45°	196	147
55°	46	50
65°	19	19
75°	10	11
85°	4	4
90°	0	



TEST NUMBER: P642701

CATALOG NUMBER: ML5615LSNFL259FS1E - 591WB - 1200LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3379.4
2.5°	3309.8
5°	3069.4
7.5°	2683.6
10°	2220.5
12.5°	1704.3
15°	1239.9
17.5°	919.8
20°	742.7
22.5°	650.3
25°	582.0
27.5°	516.2
30°	458.0
32.5°	402.3
35°	351.7
37.5°	306.2
40°	265.7
42.5°	229.0
45°	196.1
47.5°	153.1
50°	116.4
52.5°	79.7
55°	45.5
57.5°	30.4
60°	25.3
62.5°	22.8
65°	19.0
67.5°	16.4
70°	13.9
72.5°	11.4
75°	10.1
77.5°	8.9
80°	7.6
82.5°	6.3
85°	3.8
87.5°	2.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)